



The right fit for your high-output applications

Centium T12 Rapid Start

No matter what the conditions require, operating at a variety of line voltages between 120V to 480V, whether located in high ambient temperature environments (requiring a 90° C rating) or not, our family of Philips Advance Centium ballasts are ideal for a wide variety of applications.

Benefits

- IntelliVolt™ versions now available, 1/2-lamp operation of 4' 34/40W T12 lamps
- Improved efficiency over magnetic counterparts
- Lighter weight with the same mounting and wiring configuration

Features

- IntelliVolt versions now available, 1/2-lamp operation of 4' 34/40W T12 lamps
- Improved efficiency over magnetic counterparts
- Lighter weight with the same mounting and wiring configuration

Application

- Retail, commercial, institutional and industrial applications including: schools, offices, specialty & department stores, warehouses and manufacturing


Centium T12 Rapid Start

Versions



ICN2S40N35I

Dimensional drawing



Product	A1	A2	B1	C1
CENTIUM ICN2S40N35M	9.50 in	8.90 in	1.30 in	1.00 in
CENTIUM ICN2S40N35I	9.50 in	8.90 in	1.30 in	1.00 in

