



The right choice for a broad range of new construction and retrofit applications

Optanium T8 Instant Start

Reliable and energy efficient Philips Advance's Centium commercial grade specifications, plus added benefits of lamp striation reduction technology.

Benefits

- Compatible with Energy Saving lamps
- Eligible for Utility Rebates
- Maximizes fixture design
- Reduces packaging waste

Features

- IntelliVolt (120-277V) input voltage range
- Lamp Striation Reduction
- Meets NEMA Premium/CEE
- Smallest enclosure in industry

Application


- General office lighting, institutional, government, health care, school applications

Optanium T8 Instant Start

Versions



Dimensional drawing



Product	A1	A2	B1	C1
OPTANIUM GOPA3P32SC35M	9.5 in	8.90 in	1.7 in	1.18 in
OPTANIUM GOPA4P32SC35M	9.5 in	8.90 in	1.7 in	1.18 in

Operating and Electrical	
Input Frequency	50 to 60 Hz
Input Voltage	347 V
Total Harmonic Distortion USA	10 %
General Information	
Lamp Type	F32T8
Mechanical and Housing	
Housing	SC

General Information

Order Code	Full Product Name	Number Of Lamps
913710851602	OPTANIUM ELE BALLAST (4) F32T8 347V	3/4 piece/unit

Order Code	Full Product Name	Number Of Lamps
913710894702	OPTANIUM ELE BALLAST (3) F32T8 347V	2/3 piece/unit

Optanium T8 Instant Start

