



Compact designs, unlimited possibilities

e-Vision Low Wattage 20-150W

Low frequency electronic HID ballasts such as the Philips Advance e-Vision line constantly measure and adjust the wattage, optimizing delivery of the ceramic lamps' superior color properties. This makes ceramic metal halide operated by e-Vision ballasts the premier choice for many applications previously illuminated by either tungsten halogen or incandescent sources, such as retail lighting.

优点

- Constant lamp wattage for optimal color control and maximum performance
- Significant energy savings can be achieved when compared to incandescent or magnetic alternatives

特点

- Low frequency lamp operation
- Intellivolt 120-277V input range
- Metallic enclosures for optimal thermal dissipation
- Smaller and lighter weight than magnetic HID ballasts
- Thermally protected, internally fused, and output short circuit protected with Lamp End-of-Life shutdown

应用


- Retail display and accent lighting in both track and downlights, lobbies, atriums, landscape and façade lighting

e-Vision Low Wattage 20-150W

Versions



二维绘图



Product	A1	A2	A3	A4	A5	B1	B2	C1
E-VISION ELE MH BAL 39W	3.8 in	3.5 in	3.4 in	2.0 in	1.13 in	3.0 in	2.6 in	1.2 in
M130 120-277 50/60HZ								

