



Maximum performance under all weather conditions

SignPRO

Philips Advance signPRO line...a brand synonymous with full-line, high-quality sign ballasts offered exclusively to the sign industry to support the market's broad range of sign applications, now adds: ...four new energy-efficient signPRO Electronic Fluorescent Sign Ballasts for T8/HO and T12/HO High Output (800mA) Lamps.

Philips Advance signPRO line...a brand synonymous with full-line, high-quality sign ballasts offered exclusively to the sign industry to support the market's broad range of sign applications, now adds: ...four new energy-efficient signPRO Electronic Fluorescent Sign Ballasts for T8/HO and T12/HO High Output (800mA) Lamps.

Avantages

- Simplifies inventory needs with wide range of input voltages
- Flexible multiple lamp operation
- Smart replacement for banned magnetic rapid start sign ballasts

Fonctions

- IntelliVolt operation: 120V to 277V, 50/60 Hz,
- Energy-efficient, DOE Nov. 14, 2014 compliant,
- Instant Start, parallel lamp operation,
- Dependable starting down to -20°F,
- Designed for T8/HO and T12/HO High Output (800mA) Lamps


Application

- Indoor and outdoor electronic signs

Versions



Schéma dimensionnel



Product	A1	A2	B1	C1
SIGNPRO MAG ISB104014EI	14,31 in	13,75 in	3,19 in	2,63 in
SIGNPRO MAG ISB021612EI	9,64 in	9 in	1,69 in	1,13 in
SIGNPRO MAG ISB043214EI	14,31 in	13,75 in	3,19 in	2,63 in
SIGNPRO MAG ISB084846EI	14,31 in	13,75 in	3,19 in	2,63 in

Fonctionnement et électricité

Fréquence d'entrée	50 à 60 Hz
Tension d'entrée	120 to 277 V
Distorsion harmonique totale États-Unis	10 %

Renseignements généraux

Type de lampe	T12/HO
---------------	--------

Renseignements généraux

Order Code	Full Product Name	Nombre de lampes
503722	SIGNPRO MAG ELE SIGN BAL (1-2) T12HO 2-16FT 120-277V	1-2 piece/unit
503730	SIGNPRO MAG ELE SIGN BAL (1-4) T12HO 4-32FT 120-277V	1-4 piece/unit

Order Code	Full Product Name	Nombre de lampes
503748	SIGNPRO MAG ELE SIGN BAL (4-6) T12HO 8-48FT 120-277V	4-6 piece/unit
503755	SIGNPRO MAG ELE SIGN BAL (1-4)T12HO 10-40FT 120-277V	1-4 piece/unit

Mécanique et boîtier

Order Code	Full Product Name	Boîtier
503722	SIGNPRO MAG ELE SIGN BAL (1-2) T12HO 2-16FT 120-277V	BL1
503730	SIGNPRO MAG ELE SIGN BAL (1-4) T12HO 4-32FT 120-277V	BL2

Order Code	Full Product Name	Boîtier
503748	SIGNPRO MAG ELE SIGN BAL (4-6) T12HO 8-48FT 120-277V	BL2
503755	SIGNPRO MAG ELE SIGN BAL (1-4)T12HO 10-40FT 120-277V	BL2

