



Reliable performance

Core & Coil (71A) MH 175W - 450W

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Beneficios

- Vacuum-pressure impregnation is used to re-enforce the electrical insulation of the ballast, preclude moisture, inhibit noise, and dissipate heat
- Pre-insulated voltage leads reduce the risk of shock and shrink installation time

Características


- Vacuum-pressure impregnated with a silica-filled polyester varnish
- All core and coil ballasts below 600W utilize a UL Class H (180°C) insulation system
- C and C ballasts 600W and higher utilize a UL Class N (200°C) insulation system
- Pre-insulated voltage leads
- Ballast kits supplied with pre-wired ignitor

Aplicaciones

- High bay retail, manufacturing, gymnasiums, warehouses, parking structures, outdoor

Core & Coil (71A) MH 175W - 450W


Versions



71A55N0500

Core & Coil (71A) MH 175W - 450W

Plano de dimensiones



Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A5742520DTEE	4.05 in	2.15 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A6042600TAAE	3.90 in	2.10 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A60N1500	3.7 in	2.15 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5741001D	4.2 in	3 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A5792500DMLA	3.10 in	1.5 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5742510DTEE	4.05 in	2.15 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5590500D	3.95 in	2.42 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A57N2500D	3.25 in	1.75 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5692520DEE	4.20 in	2.95 in				
CORE & COIL HID 71A57A2500D	3.1 in	1.5 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5593500DML	3.5 in	2.24 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A6092001D	4.1 in	2.16 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A60A1500DA	4.00 in	2.15 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5541500DTEE	3.7 in	1.8 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5590500DML	3.95 in	2.42 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A61E6500D	3.8 in	2.2 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5540001D	4 in	2.4 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A57A0001D	3.1 in	1.64 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5792500DEE	3.55 in	1.61 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A6091500DA	4 in	2.13 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A6091500DMLA	4 in	2.13 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A57A0600A	3.10 in	1.64 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A6042510DTAAE	3.90 in	2.10 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A6092500DMLA	4.10 in	2.10 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A6042001D	3.9 in	2.11 in	4.8 in	4.4 in	4.3 in	3.9 in

Core & Coil (71A) MH 175W - 450W

Plano de dimensiones

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A5943500DTAEE	4.15 in	2.20 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5790500DA	3.15 in	1.5 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5590510D	3.95 in	2.42 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A5892500DMLA	3.65 in	1.8 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A55A0500D	4.02 in	2.41 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A55A0001D	4.02 in	2.41 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A60E6500	4 in	2.4 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A55A0600	4.02 in	2.41 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A5543500DTEE	4.20 in	3.10 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A60A2500DA	3.80 in	1.97 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5892001D	3.65 in	1.8 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A60A1600A	4 in	2.15 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5943600TAEE	4.15 in	2.20 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5593001D	3.5 in	2.24 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A5593600EE	4.41 in	3.20 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A5752001D	4 in	2.2 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5792600EE	3.55 in	1.61 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5842001DT	3.65 in	1.77 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5750001D	3.1 in	1.6 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5842500DTAEE	4.10 in	2.20 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5792001D	3.1 in	1.5 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5993500DAEE	4.05 in	2.13 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A58A2500DA	3.65 in	1.8 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5692500DEE	4.20 in	2.95 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A6092500DAEE	4.10 in	2.16 in	4.8 in	4.4 in	4.3 in	3.9 in

Core & Coil (71A) MH 175W - 450W

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A5543600TEE	4.20 in	3.10 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A5993600AEE	4.05 in	2.13 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5770001D	3.15 in	1.6 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5993001D	3.65 in	1.8 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5771001D	4.2 in	3 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A5791500D	4.2 in	3 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A5591500DEE	3.30 in	1.65 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A56A2500D	3.6 in	2.45 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A57A0500D	3.1 in	1.64 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A57N0500D	3.4 in	1.78 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5692001D	3.6 in	2.45 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A6051001D	4.45 in	2.34 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5692510DEE	4.20 in	2.95 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A5742500DTEE	4.05 in	2.15 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A59A3500DA	3.65 in	1.8 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5892600AEE	3.77 in	2.06 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5792500DXEE	4.05 in	2.15 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A55A0610	4.02 in	2.41 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A60H1500DMLA	4.05 in	2.14 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A60A2600A	3.80 in	1.97 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5742600TEE	4.05 in	2.15 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A6041001D	4 in	2.13 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5570001D	3.95 in	2.42 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A6052001D	4.3 in	2.2 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A6091510DA	4 in	2.13 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A6071001D	4 in	2.13 in	4.8 in	4.4 in	4.3 in	3.9 in

Core & Coil (71A) MH 175W - 450W

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID 71A55A3500D	3.5 in	2.24 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A6343500DTEE	4.15 in	2.40 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A60A1001D	4 in	2.15 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A55H0500DML	3.87 in	2.4 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A58N2500D	3.8 in	2.05 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5892500DAEE	3.77 in	2.06 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5593510DEE	4.41 in	3.20 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A5642500DTEE	4.15 in	2.90 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A6041500DMLA	4 in	2.13 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A55N0500	4 in	2.75 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A5790500DMLA	165.1 mm	88.9 mm	111.76 mm	146.05 mm		
CORE & COIL HID 71A57H0500DMLA	3.15 in	1.65 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A6092600AEE	4.10 in	2.16 in	4.8 in	4.4 in	4.3 in	3.9 in
CORE & COIL HID 71A5593500DEE	4.41 in	3.20 in	3.9 in	3.5 in	2.8 in	2.4 in
CORE & COIL HID 71A60N2500D	3.8 in	2.04 in	4.8 in	4.4 in	4.3 in	3.9 in

General Information

Number Of Lamps	1 piece/unit
-----------------	--------------

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Input Voltage
71A55N0500	CORE & COIL HID MH BAL 175W M57 120/220-240V 50HZ C&C	50 Hz	120/220-240 V
71A57N0500D	CORE & COIL HID MH BAL 250W M58 120/220-240V 50HZ C&C	50 Hz	120/220-240 V
71A57A2500D	CORE & COIL HID MH BAL 250W M138/M153 120/277/347V C&C	60 Hz	120/277/347 V
71A55A3500D	CORE & COIL HID MH BAL 175W M137/M152 120/277/347V C&C	60 Hz	120/277/347 V

Order Code	Full Product Name	Input Frequency	Input Voltage
71A5593001D	CORE & COIL HID MH BAL 175W M137/M152 QUAD KIT	60 Hz	120/208/240/277 V
71A55A0500D	CORE & COIL HID MH BAL 175W M57 120/277/347V C&C	60 Hz	120/277/347 V
71A55A0600	CORE & COIL HID MH BAL 175W M57 120/277/347V C&C	60 Hz	120/277/347 V
71A55A0610	CORE & COIL HID MH BAL 175W M57 120/277/347V C&C	60 Hz	120/277/347 V
71A5741001D	CORE & COIL HID MH BAL 250W M58 480V KIT	60 Hz	480 V
71A60A1500DA	CORE & COIL HID MH BAL 400W M59 120/277/347V C&C	60 Hz	120/277/347 V

Core & Coil (71A) MH 175W - 450W

Order Code	Full Product Name	Input Frequency	Input Voltage
71A57A0500D	CORE & COIL HID MH BAL 250W M58 120/277/347V C&C	60 Hz	120/277/347 V
71A5791500D	CORE & COIL HID MH BAL 250W M58 QUAD C&C	60 Hz	120/208/240/277 V
71A55A0001D	CORE & COIL HID MH BAL 175W M57 120/277/347V KIT	60 Hz	120/277/347 V
71A57A0001D	CORE & COIL HID MH BAL 250W M58 120/277/347V KIT	60 Hz	120/277/347 V
71A6071001D	CORE & COIL HID MH BAL 400W M59 QUAD KIT	60 Hz	120/208/240/277 V
71A60A1001D	CORE & COIL HID MH BAL 400W M59 120/277/347V KIT	60 Hz	120/277/347 V
71A5570001D	CORE & COIL HID MH BAL 175W M57 QUAD KIT	60 Hz	120/208/240/277 V
71A5692001D	CORE & COIL HID MH BAL 200W M136 QUAD KIT	60 Hz	120/208/240/277 V
71A56A2500D	CORE & COIL HID MH BAL 200W M136 120/277/347V C&C	60 Hz	120/277/347 V
71A5770001D	CORE & COIL HID MH BAL 250W M58 QUAD KIT	60 Hz	120/208/240/277 V
71A5771001D	CORE & COIL HID MH BAL 250W M58 QUAD KIT	60 Hz	120/208/240/277 V
71A5892001D	CORE & COIL HID MH BAL 320W M132/154 QUAD KIT	60 Hz	120/208/240/277 V
71A5993001D	CORE & COIL HID MH BAL 350W M131 QUAD KIT	60 Hz	120/208/240/277 V
71A6041001D	CORE & COIL HID MH BAL 400W M59 480V/120T KIT	60 Hz	480/120T V
71A6092001D	CORE & COIL HID MH BAL 400W M135/155 QUAD KIT	60 Hz	120/208/240/277 V
71A60E6500	CORE & COIL HID MH BAL 400W M59 120/208/240V C&C	60 Hz	120/208/240 V
71A61E6500D	CORE & COIL HID MH BAL 400W M135/155 120/208/240V C&C	60 Hz	120/208/240 V
71A5540001D	CORE & COIL HID MH BAL 175W M57 480V KIT	60 Hz	480 V
71A60N1500	CORE & COIL HID MH BAL 400W M59 120/220-240V 50HZ C&C	50 Hz	120/220-240 V
71A5590500D	CORE & COIL HID MH BAL 175W M57 QUAD C&C	60 Hz	120/208/240/277 V
71A5541500DTEE	CORE & COIL HID MH BAL 175W M137/M152 480V/120T C&C	60 Hz	480/120T V
71A55H0500DML	CORE & COIL HID MH BAL 175W M57 127/220V C&C	60 Hz	127/220 V
71A57H0500DMLA	CORE & COIL HID MH BAL 250W M58 127/220V C&C	60 Hz	127/220 V
71A60H1500DMLA	CORE & COIL HID MH BAL 400W M59 127/220V C&C	60 Hz	127/220 V

Order Code	Full Product Name	Input Frequency	Input Voltage
71A6052001D	CORE & COIL HID MH BAL 400W M135/M155 5-TAP KIT	60 Hz	120/208/240/277/480 V
71A5792500DXEE	CORE & COIL HID MH BAL 250W M138/M153 QUAD C&C	60 Hz	120/208/240/277 V
71A5752001D	CORE & COIL HID MH BAL 250W M138/M153 5-TAP KIT	60 Hz	120/208/240/277/480 V
71A6042001D	CORE & COIL HID MH BAL 400W M135/155 480V/120T KIT	60 Hz	480/120T V
71A5750001D	CORE & COIL HID MH BAL 250W M58 5-TAP KIT	60 Hz	120/208/240/277/480 V
71A5792001D	CORE & COIL HID MH BAL 250W M138/M153 QUAD KIT	60 Hz	120/208/240/277 V
71A6051001D	CORE & COIL HID MH BAL 400W M59 5-TAP KIT	60 Hz	120/208/240/277/480 V
71A57N2500D	CORE & COIL HID MH BAL 250W M138/153 120/220-240 50HZ CC	50 Hz	120/220-240 V
71A58N2500D	CORE & COIL HID MH BAL 320W M132/154 120/220-240V 50HZ	50 Hz	120/220-240 V
71A60N2500D	CORE & COIL HID MH BAL 400W M135/155 120/220-240V 50HZ	50 Hz	120/220-240 V
71A5590510D	CORE & COIL HID MH BAL 175W M57 QUAD C&C	60 Hz	120/208/240/277 V
71A6091510DA	CORE & COIL HID MH BAL 400W M59 QUAD C&C	60 Hz	120/208/240/277 V
71A5590500DML	CORE & COIL HID MH BAL 175W M57 QUAD C&C	60 Hz	120/208/240/277 V
71A5593500DML	CORE & COIL HID MH BAL 175W M137 OR M152 QUAD C&C	60 Hz	120/208/240/277 V
71A5790500DA	CORE & COIL HID MH BAL 250W M58/H37 QUAD C&C	60 Hz	120/208/240/277 V
71A5892500DMLA	CORE & COIL HID MH BAL 320W M132/M154 QUAD C&C	60 Hz	120/208/240/277 V
71A6091500DA	CORE & COIL HID MH BAL 400W M59 QUAD C&C	60 Hz	120/208/240/277 V
71A6091500DMLA	CORE & COIL HID MH BAL 400W M59 QUAD C&C	60 Hz	120/208/240/277 V
71A58A2500DA	CORE & COIL HID MH BAL 320W M132/154 120/277/347V C&C	60 Hz	120/277/347 V
71A59A3500DA	CORE & COIL HID MH BAL 350W M131 120/277/347V C&C	60 Hz	120/277/347 V
71A60A2500DA	CORE & COIL HID MH BAL 400W M135/155 120/277/347V C&C	60 Hz	120/277/347 V
71A60A1600A	CORE & COIL HID MH BAL 400W M59 120/277/347V C&C	60 Hz	120/277/347 V

Core & Coil (71A) MH 175W - 450W

Order Code	Full Product Name	Input	
		Frequency	Input Voltage
71A5842001DT	CORE & COIL HID MH BAL 320W M132/154 480V/120T KIT	60 Hz	480/120T V
71A60A2600A	CORE & COIL HID MH BAL 400W M135/M155 120/277/347V C&C	60 Hz	120/277/347 V
71A5792500DMLA	CORE & COIL HID MH BAL 250W M138/M153 QUAD C&C	60 Hz	120/208/240/277 V
71A57A0600A	CORE & COIL HID MH BAL 250W M58 120/277/347V C&C	60 Hz	120/277/347 V
71A6041500DMLA	CORE & COIL HID MH BAL 400W M59/H33 480V C&C	60 Hz	480 V
71A6092500DMLA	CORE & COIL HID MH BAL 400W M135/155/172 QUAD C&C	60 Hz	120/208/240/277 V
71A5790500DMLA	CORE & COIL HID MH BAL 250W M58/H37 QUAD C&C	60 Hz	120/208/240/277 V
71A5593500DEE	CORE & COIL HID MH BAL 175W M137/M152 QUAD C&C	60 Hz	120/208/240/277 V
71A5591500DEE	CORE & COIL HID MH BAL 175W M137/M152 QUAD C&C	60 Hz	120/208/240/277 V
71A5543500DTEE	CORE & COIL HID MH BAL 175W M137/M152 480V/120T C&C	60 Hz	480/120T V
71A5692500DEE	CORE & COIL HID MH BAL 200W M136 QUAD C&C	60 Hz	120/208/240/277 V
71A5642500DTEE	CORE & COIL HID MH BAL 200W M136 480V/120T C&C	60 Hz	480/120T V
71A5742500DTEE	CORE & COIL HID MH BAL 250W M138/M153 480V/120T C&C	60 Hz	480/120T V
71A5792500DEE	CORE & COIL HID MH BAL 250W M138/M153 QUAD C&C	60 Hz	120/208/240/277 V
71A5842500DTAEE	CORE & COIL HID MH BAL 320W M132/M154 480V/120T C&C	60 Hz	480/120T V
71A5892500DAEE	CORE & COIL HID MH BAL 320W M132/M154 QUAD C&C	60 Hz	120/208/240/277 V
71A5943500DTAEE	CORE & COIL HID MH BAL 350W M131 480V/120T C&C	60 Hz	480/120T V
71A5993500DAEE	CORE & COIL HID MH BAL 350W M131 QUAD C&C	60 Hz	120/208/240/277 V

Order Code	Full Product Name	Input	
		Frequency	Input Voltage
71A5892600AEE	CORE & COIL HID MH BAL 320W M132/M154 QUAD C&C	60 Hz	120/208/240/277 V
71A5993600AEE	CORE & COIL HID MH BAL 350W M131 QUAD C&C	60 Hz	120/208/240/277 V
71A5943600TAEE	CORE & COIL HID MH BAL 350W M131 480V/120T C&C	60 Hz	480/120T V
71A6092500DAEE	CORE & COIL HID MH BAL 400W M135/155 QUAD C&C	60 Hz	120/208/240/277 V
71A6092600AEE	CORE & COIL HID MH BAL 400W M135/155 QUAD C&C	60 Hz	120/208/240/277 V
71A6042510DTAEE	CORE & COIL HID MH BAL 400W M135/155 480V/120T C&C	60 Hz	480/120T V
71A6042600TAEE	CORE & COIL HID MH BAL 400W M135/155 480V/120T C&C	60 Hz	480/120T V
71A5593600EE	CORE & COIL HID MH BAL 175W M137/M152 QUAD C&C	60 Hz	120/208/240/277 V
71A5692510DEE	CORE & COIL HID MH BAL 200W M136 QUAD C&C	60 Hz	120/208/240/277 V
71A5742510DTEE	CORE & COIL HID MH BAL 250W M138/153 480V/120T C&C	60 Hz	480/120T V
71A5792600EE	CORE & COIL HID MH BAL 250W M138/M153 QUAD C&C	60 Hz	120/208/240/277 V
71A5543600TEE	CORE & COIL HID MH BAL 175W M137/152 480V/120T C&C	60 Hz	480/120T V
71A5593510DEE	CORE & COIL HID MH BAL 175W M137/152 QUAD C&C	60 Hz	120/208/240/277 V
71A5742520DTEE	CORE & COIL HID MH BAL 250W M138/M153 480V/120T C&C	60 Hz	480/120T V
71A5692520DEE	CORE & COIL HID MH BAL 200W M136 QUAD C&C	60 Hz	120/208/240/277 V
71A5742600TEE	CORE & COIL HID MH BAL 250W M138/M153 480V/120T C&C	60 Hz	480/120T V
71A6343500DTEE	CORE & COIL HID MH BAL 450W M144 480V/120T C&C	60 Hz	480/120T V

General Information

Order Code	Full Product Name	Capacitor	
		Value	Lamp Type
71A55N0500	CORE & COIL HID MH BAL 175W M57 120/220-240V 50HZ C&C	12 MFD	175/150W MH
71A57N0500D	CORE & COIL HID MH BAL 250W M58 120/220-240V 50HZ C&C	18 MFD	250W MH

Order Code	Full Product Name	Capacitor	
		Value	Lamp Type
71A57A2500D	CORE & COIL HID MH BAL 250W M138/M153 120/277/347V C&C	17 MFD	250W MH
71A55A3500D	CORE & COIL HID MH BAL 175W M137/M152 120/277/347V C&C	11 MFD	175W MH

Core & Coil (71A) MH 175W - 450W

Order Code	Full Product Name	Capacitor	
		Value	Lamp Type
71A5593001D	CORE & COIL HID MH BAL 175W M137/M152 QUAD KIT	11 MFD	175W MH
71A55A0500D	CORE & COIL HID MH BAL 175W M57 120/277/347V C&C	10 MFD	175/150W MH
71A55A0600	CORE & COIL HID MH BAL 175W M57 120/277/347V C&C	10 MFD	175/150W MH
71A55A0610	CORE & COIL HID MH BAL 175W M57 120/277/347V C&C	10 MFD	175/150W MH
71A5741001D	CORE & COIL HID MH BAL 250W M58 480V KIT	15 MFD	250W MH
71A60A1500DA	CORE & COIL HID MH BAL 400W M59 120/277/347V C&C	24 MFD	400W MH
71A57A0500D	CORE & COIL HID MH BAL 250W M58 120/277/347V C&C	15 MFD	250W MH
71A5791500D	CORE & COIL HID MH BAL 250W M58 QUAD C&C	15 MFD	250W MH
71A55A0001D	CORE & COIL HID MH BAL 175W M57 120/277/347V KIT	10 MFD	175/150W MH
71A57A0001D	CORE & COIL HID MH BAL 250W M58 120/277/347V KIT	15 MFD	250W MH
71A6071001D	CORE & COIL HID MH BAL 400W M59 QUAD KIT	24 MFD	400W MH
71A60A1001D	CORE & COIL HID MH BAL 400W M59 120/277/347V KIT	24 MFD	400W MH
71A5570001D	CORE & COIL HID MH BAL 175W M57 QUAD KIT	10 MFD	175/150W MH
71A5692001D	CORE & COIL HID MH BAL 200W M136 QUAD KIT	15 MFD	200W MH
71A56A2500D	CORE & COIL HID MH BAL 200W M136 120/277/347V C&C	15 MFD	200W MH
71A5770001D	CORE & COIL HID MH BAL 250W M58 QUAD KIT	15 MFD	250W MH
71A5771001D	CORE & COIL HID MH BAL 250W M58 QUAD KIT	15 MFD	250W MH
71A5892001D	CORE & COIL HID MH BAL 320W M132/154 QUAD KIT	21 MFD	320W MH
71A5993001D	CORE & COIL HID MH BAL 350W M131 QUAD KIT	22.5 MFD	350W MH
71A6041001D	CORE & COIL HID MH BAL 400W M59 480V/120T KIT	24 MFD	400W MH
71A6092001D	CORE & COIL HID MH BAL 400W M135/155 QUAD KIT	26 MFD	400W MH
71A60E6500	CORE & COIL HID MH BAL 400W M59 120/208/240V C&C	20 MFD	400W MH
71A61E6500D	CORE & COIL HID MH BAL 400W M135/155 120/208/240V C&C	26 MFD	400W MH
71A5540001D	CORE & COIL HID MH BAL 175W M57 480V KIT	10 MFD	175/150W MH
71A60N1500	CORE & COIL HID MH BAL 400W M59 120/220-240V 50HZ C&C	24 MFD	400W MH

Order Code	Full Product Name	Capacitor	
		Value	Lamp Type
71A5590500D	CORE & COIL HID MH BAL 175W M57 QUAD C&C	10 MFD	175/150W MH
71A5541500DTEE	CORE & COIL HID MH BAL 175W M137/M152 480V/120T C&C	11 MFD	175W MH
71A55H0500DML	CORE & COIL HID MH BAL 175W M57 127/220V C&C	10 MFD	175/150W MH
71A57H0500DMLA	CORE & COIL HID MH BAL 250W M58 127/220V C&C	15 MFD	250W MH
71A60H1500DMLA	CORE & COIL HID MH BAL 400W M59 127/220V C&C	24 MFD	400W MH
71A6052001D	CORE & COIL HID MH BAL 400W M135/M155 5-TAP KIT	26 MFD	400W MH
71A5792500DXEE	CORE & COIL HID MH BAL 250W M138/M153 QUAD C&C	17 MFD	250W MH
71A5752001D	CORE & COIL HID MH BAL 250W M138/M153 5-TAP KIT	17 MFD	250W MH
71A6042001D	CORE & COIL HID MH BAL 400W M135/155 480V/120T KIT	26 MFD	400W MH
71A5750001D	CORE & COIL HID MH BAL 250W M58 5-TAP KIT	15 MFD	250W MH
71A5792001D	CORE & COIL HID MH BAL 250W M138/M153 QUAD KIT	17 MFD	250W MH
71A6051001D	CORE & COIL HID MH BAL 400W M59 5-TAP KIT	24 MFD	400W MH
71A57N2500D	CORE & COIL HID MH BAL 250W M138/153 120/220-240 50HZ CC	20 MFD	250W MH
71A58N2500D	CORE & COIL HID MH BAL 320W M132/154 120/220-240V 50HZ	24 MFD	320W MH
71A60N2500D	CORE & COIL HID MH BAL 400W M135/155 120/220-240V 50HZ	30 MFD	400W MH
71A5590510D	CORE & COIL HID MH BAL 175W M57 QUAD C&C	10 MFD	175/150W MH
71A6091510DA	CORE & COIL HID MH BAL 400W M59 QUAD C&C	24 MFD	400W MH
71A5590500DML	CORE & COIL HID MH BAL 175W M57 QUAD C&C	10 MFD	175/150W MH
71A5593500DML	CORE & COIL HID MH BAL 175W M137 OR M152 QUAD C&C	11 MFD	175W MH
71A5790500DA	CORE & COIL HID MH BAL 250W M58/H37 QUAD C&C	15 MFD	250W MH
71A5892500DMLA	CORE & COIL HID MH BAL 320W M132/M154 QUAD C&C	21 MFD	320W MH
71A6091500DA	CORE & COIL HID MH BAL 400W M59 QUAD C&C	24 MFD	400W MH
71A6091500DMLA	CORE & COIL HID MH BAL 400W M59 QUAD C&C	24 MFD	400W MH
71A58A2500DA	CORE & COIL HID MH BAL 320W M132/154 120/277/347V C&C	21 MFD	320W MH
71A59A3500DA	CORE & COIL HID MH BAL 350W M131 120/277/347V C&C	22.5 MFD	350W MH

Core & Coil (71A) MH 175W - 450W

Order Code	Full Product Name	Capacitor	
		Value	Lamp Type
71A60A2500DA	CORE & COIL HID MH BAL 400W M135/155 120/277/347V C&C	26 MFD	400W MH
71A60A1600A	CORE & COIL HID MH BAL 400W M59 120/277/347V C&C	24 MFD	400W MH
71A5842001DT	CORE & COIL HID MH BAL 320W M132/154 480V/120T KIT	21 MFD	320W MH
71A60A2600A	CORE & COIL HID MH BAL 400W M135/M155 120/277/347V C&C	26 MFD	400W MH
71A5792500DMLA	CORE & COIL HID MH BAL 250W M138/M153 QUAD C&C	17 MFD	250W MH
71A57A0600A	CORE & COIL HID MH BAL 250W M58 120/277/347V C&C	15 MFD	250W MH
71A6041500DMLA	CORE & COIL HID MH BAL 400W M59/H33 480V C&C	24 MFD	400W MH
71A6092500DMLA	CORE & COIL HID MH BAL 400W M135/155/172 QUAD C&C	26 MFD	400W MH
71A5790500DMLA	CORE & COIL HID MH BAL 250W M58/H37 QUAD C&C	15 MFD	250W MH
71A5593500DEE	CORE & COIL HID MH BAL 175W M137/M152 QUAD C&C	11 MFD	175W MH
71A5591500DEE	CORE & COIL HID MH BAL 175W M137/M152 QUAD C&C	11 MFD	175W MH
71A5543500DTEE	CORE & COIL HID MH BAL 175W M137/M152 480V/120T C&C	11 MFD	175W MH
71A5692500DEE	CORE & COIL HID MH BAL 200W M136 QUAD C&C	15 MFD	200W MH
71A5642500DTEE	CORE & COIL HID MH BAL 200W M136 480V/120T C&C	15 MFD	200W MH
71A5742500DTEE	CORE & COIL HID MH BAL 250W M138/M153 480V/120T C&C	17 MFD	250W MH
71A5792500DEE	CORE & COIL HID MH BAL 250W M138/M153 QUAD C&C	17 MFD	250W MH
71A5842500DTAEE	CORE & COIL HID MH BAL 320W M132/M154 480V/120T C&C	21 MFD	320W MH
71A5892500DAEE	CORE & COIL HID MH BAL 320W M132/M154 QUAD C&C	21 MFD	320W MH
71A5943500DTAEE	CORE & COIL HID MH BAL 350W M131 480V/120T C&C	22.5 MFD	350W MH

Order Code	Full Product Name	Capacitor	
		Value	Lamp Type
71A5993500DAEE	CORE & COIL HID MH BAL 350W M131 QUAD C&C	22.5 MFD	350W MH
71A5892600AEE	CORE & COIL HID MH BAL 320W M132/M154 QUAD C&C	21 MFD	320W MH
71A5993600AEE	CORE & COIL HID MH BAL 350W M131 QUAD C&C	22.5 MFD	350W MH
71A5943600TAEE	CORE & COIL HID MH BAL 350W M131 480V/120T C&C	22.5 MFD	350W MH
71A6092500DAEE	CORE & COIL HID MH BAL 400W M135/155 QUAD C&C	26 MFD	400W MH
71A6092600AEE	CORE & COIL HID MH BAL 400W M135/155 QUAD C&C	26 MFD	400W MH
71A6042510DTAEE	CORE & COIL HID MH BAL 400W M135/155 480V/120T C&C	26 MFD	400W MH
71A6042600TAEE	CORE & COIL HID MH BAL 400W M135/155 480V/120T C&C	26 MFD	400W MH
71A5593600EE	CORE & COIL HID MH BAL 175W M137/M152 QUAD C&C	11 MFD	175W MH
71A5692510DEE	CORE & COIL HID MH BAL 200W M136 QUAD C&C	15 MFD	200W MH
71A5742510DTEE	CORE & COIL HID MH BAL 250W M138/153 480V/120T C&C	17 MFD	250W MH
71A5792600EE	CORE & COIL HID MH BAL 250W M138/M153 QUAD C&C	17 MFD	250W MH
71A5543600TEE	CORE & COIL HID MH BAL 175W M137/152 480V/120T C&C	11 MFD	175W MH
71A5593510DEE	CORE & COIL HID MH BAL 175W M137/152 QUAD C&C	11 MFD	175W MH
71A5742520DTEE	CORE & COIL HID MH BAL 250W M138/M153 480V/120T C&C	17 MFD	250W MH
71A5692520DEE	CORE & COIL HID MH BAL 200W M136 QUAD C&C	15 MFD	200W MH
71A5742600TEE	CORE & COIL HID MH BAL 250W M138/M153 480V/120T C&C	17 MFD	250W MH
71A6343500DTEE	CORE & COIL HID MH BAL 450W M144 480V/120T C&C	26.5 MFD	450W MH

Mechanical and Housing

Order Code	Full Product Name	Housing
71A55N0500	CORE & COIL HID MH BAL 175W M57 120/220-240V 50HZ C&C	-
71A57N0500D	CORE & COIL HID MH BAL 250W M58 120/220-240V 50HZ C&C	-
71A57A2500D	CORE & COIL HID MH BAL 250W M138/M153 120/277/347V C&C	-
71A55A3500D	CORE & COIL HID MH BAL 175W M137/M152 120/277/347V C&C	-
71A5593001D	CORE & COIL HID MH BAL 175W M137/M152 QUAD KIT	-

Order Code	Full Product Name	Housing
71A55A0500D	CORE & COIL HID MH BAL 175W M57 120/277/347V C&C	-
71A55A0600	CORE & COIL HID MH BAL 175W M57 120/277/347V C&C	-
71A55A0610	CORE & COIL HID MH BAL 175W M57 120/277/347V C&C	-
71A5741001D	CORE & COIL HID MH BAL 250W M58 480V KIT	-
71A60A1500DA	CORE & COIL HID MH BAL 400W M59 120/277/347V C&C	NA
71A57A0500D	CORE & COIL HID MH BAL 250W M58 120/277/347V C&C	-
71A5791500D	CORE & COIL HID MH BAL 250W M58 QUAD C&C	-
71A55A0001D	CORE & COIL HID MH BAL 175W M57 120/277/347V KIT	-
71A57A0001D	CORE & COIL HID MH BAL 250W M58 120/277/347V KIT	-

Core & Coil (71A) MH 175W - 450W

Order Code	Full Product Name	Housing
71A6071001D	CORE & COIL HID MH BAL 400W M59 QUAD KIT	-
71A60A1001D	CORE & COIL HID MH BAL 400W M59 120/277/347V KIT	-
71A5570001D	CORE & COIL HID MH BAL 175W M57 QUAD KIT	-
71A5692001D	CORE & COIL HID MH BAL 200W M136 QUAD KIT	-
71A56A2500D	CORE & COIL HID MH BAL 200W M136 120/277/347V C&C	-
71A5770001D	CORE & COIL HID MH BAL 250W M58 QUAD KIT	-
71A5771001D	CORE & COIL HID MH BAL 250W M58 QUAD KIT	-
71A5892001D	CORE & COIL HID MH BAL 320W M132/154 QUAD KIT	-
71A5993001D	CORE & COIL HID MH BAL 350W M131 QUAD KIT	-
71A6041001D	CORE & COIL HID MH BAL 400W M59 480V/120T KIT	-
71A6092001D	CORE & COIL HID MH BAL 400W M135/155 QUAD KIT	-
71A60E6500	CORE & COIL HID MH BAL 400W M59 120/208/240V C&C	-
71A61E6500D	CORE & COIL HID MH BAL 400W M135/155 120/208/240V C&C	-
71A5540001D	CORE & COIL HID MH BAL 175W M57 480V KIT	-
71A60N1500	CORE & COIL HID MH BAL 400W M59 120/220-240V 50HZ C&C	-
71A5590500D	CORE & COIL HID MH BAL 175W M57 QUAD C&C	-
71A5541500DTEE	CORE & COIL HID MH BAL 175W M137/M152 480V/120T C&C	-
71A55H0500DML	CORE & COIL HID MH BAL 175W M57 127/220V C&C	-
71A57H0500DMLA	CORE & COIL HID MH BAL 250W M58 127/220V C&C	-
71A60H1500DMLA	CORE & COIL HID MH BAL 400W M59 127/220V C&C	-
71A6052001D	CORE & COIL HID MH BAL 400W M135/M155 5-TAP KIT	-
71A5792500DXEE	CORE & COIL HID MH BAL 250W M138/M153 QUAD C&C	-
71A5752001D	CORE & COIL HID MH BAL 250W M138/M153 5-TAP KIT	-
71A6042001D	CORE & COIL HID MH BAL 400W M135/155 480V/120T KIT	-
71A5750001D	CORE & COIL HID MH BAL 250W M58 5-TAP KIT	-
71A5792001D	CORE & COIL HID MH BAL 250W M138/M153 QUAD KIT	-
71A6051001D	CORE & COIL HID MH BAL 400W M59 5-TAP KIT	-
71A57N2500D	CORE & COIL HID MH BAL 250W M138/153 120/220-240 50HZ CC	-
71A58N2500D	CORE & COIL HID MH BAL 320W M132/154 120/220-240V 50HZ	-
71A60N2500D	CORE & COIL HID MH BAL 400W M135/155 120/220-240V 50HZ	-
71A5590510D	CORE & COIL HID MH BAL 175W M57 QUAD C&C	-
71A6091510DA	CORE & COIL HID MH BAL 400W M59 QUAD C&C	-
71A5590500DML	CORE & COIL HID MH BAL 175W M57 QUAD C&C	-
71A5593500DML	CORE & COIL HID MH BAL 175W M137 OR M152 QUAD C&C	-
71A5790500DA	CORE & COIL HID MH BAL 250W M58/H37 QUAD C&C	-
71A5892500DMLA	CORE & COIL HID MH BAL 320W M132/M154 QUAD C&C	-
71A6091500DA	CORE & COIL HID MH BAL 400W M59 QUAD C&C	-
71A6091500DMLA	CORE & COIL HID MH BAL 400W M59 QUAD C&C	-
71A58A2500DA	CORE & COIL HID MH BAL 320W M132/154 120/277/347V C&C	-

Order Code	Full Product Name	Housing
71A59A3500DA	CORE & COIL HID MH BAL 350W M131 120/277/347V C&C	-
71A60A2500DA	CORE & COIL HID MH BAL 400W M135/155 120/277/347V C&C	-
71A60A1600A	CORE & COIL HID MH BAL 400W M59 120/277/347V C&C	-
71A5842001DT	CORE & COIL HID MH BAL 320W M132/154 480V/120T KIT	-
71A60A2600A	CORE & COIL HID MH BAL 400W M135/M155 120/277/347V C&C	-
71A5792500DMLA	CORE & COIL HID MH BAL 250W M138/M153 QUAD C&C	-
71A57A0600A	CORE & COIL HID MH BAL 250W M58 120/277/347V C&C	-
71A6041500DMLA	CORE & COIL HID MH BAL 400W M59/H33 480V C&C	-
71A6092500DMLA	CORE & COIL HID MH BAL 400W M135/155/172 QUAD C&C	-
71A5790500DMLA	CORE & COIL HID MH BAL 250W M58/H37 QUAD C&C	-
71A5593500DEE	CORE & COIL HID MH BAL 175W M137/M152 QUAD C&C	-
71A5591500DEE	CORE & COIL HID MH BAL 175W M137/M152 QUAD C&C	-
71A5543500DTEE	CORE & COIL HID MH BAL 175W M137/M152 480V/120T C&C	-
71A5692500DEE	CORE & COIL HID MH BAL 200W M136 QUAD C&C	-
71A5642500DTEE	CORE & COIL HID MH BAL 200W M136 480V/120T C&C	-
71A5742500DTEE	CORE & COIL HID MH BAL 250W M138/M153 480V/120T C&C	-
71A5792500DEE	CORE & COIL HID MH BAL 250W M138/M153 QUAD C&C	-
71A5842500DTAEE	CORE & COIL HID MH BAL 320W M132/M154 480V/120T C&C	-
71A5892500DAEE	CORE & COIL HID MH BAL 320W M132/M154 QUAD C&C	-
71A5943500DTAEE	CORE & COIL HID MH BAL 350W M131 480V/120T C&C	-
71A5993500DAEE	CORE & COIL HID MH BAL 350W M131 QUAD C&C	-
71A5892600AEE	CORE & COIL HID MH BAL 320W M132/M154 QUAD C&C	-
71A5993600AEE	CORE & COIL HID MH BAL 350W M131 QUAD C&C	-
71A5943600TAEE	CORE & COIL HID MH BAL 350W M131 480V/120T C&C	-
71A6092500DAEE	CORE & COIL HID MH BAL 400W M135/155 QUAD C&C	-
71A6092600AEE	CORE & COIL HID MH BAL 400W M135/155 QUAD C&C	-
71A6042510DTAEE	CORE & COIL HID MH BAL 400W M135/155 480V/120T C&C	-
71A6042600TAEE	CORE & COIL HID MH BAL 400W M135/155 480V/120T C&C	-
71A5593600EE	CORE & COIL HID MH BAL 175W M137/M152 QUAD C&C	-
71A5692510DEE	CORE & COIL HID MH BAL 200W M136 QUAD C&C	-
71A5742510DTEE	CORE & COIL HID MH BAL 250W M138/153 480V/120T C&C	-
71A5792600EE	CORE & COIL HID MH BAL 250W M138/M153 QUAD C&C	-
71A5543600TEE	CORE & COIL HID MH BAL 175W M137/152 480V/120T C&C	-
71A5593510DEE	CORE & COIL HID MH BAL 175W M137/152 QUAD C&C	-
71A5742520DTEE	CORE & COIL HID MH BAL 250W M138/M153 480V/120T C&C	-
71A5692520DEE	CORE & COIL HID MH BAL 200W M136 QUAD C&C	NA
71A5742600TEE	CORE & COIL HID MH BAL 250W M138/M153 480V/120T C&C	-
71A6343500DTEE	CORE & COIL HID MH BAL 450W M144 480V/120T C&C	-

Core & Coil (71A) MH 175W - 450W

