



# Quiet, reliable operation

## Encapsulated Core & Coil (73B)

Where quiet performance is required, the standard open core and coil ballast is encapsulated (potted) in a cube-shaped steel can utilizing Class H (180°C) polyester compound.

### Avantages

- Quiet operation
- Includes the benefits of the open core and coil above

### Fonctions

- Class A noise rating through 175W and Class B noise rating for 250W and 400W
- Includes the features of the open core and coil above

### Application


- Offices, schools, and retail stores

### Versions



## Encapsulated Core & Coil (73B)

### Schéma dimensionnel



Product	A1	A2	A3	B1	B2	C1	D1
ENCAPSULATED CORE & COIL HID 73B5790500DA	6,75 in	6 in	5,4 in	3,8 in	2 in	5 in	0,25 in

