



All-weather performance and reliability

Outdoor Weatherproof (79W)

Outdoor weatherproof ballasts are designed for remote mounting outdoors under all weather conditions. They may also be placed inside a pole base, but care must be taken to avoid areas prone to flood situations as they are not water submersable.

Avantages

- Ballast is suitable for use in most outdoor weather conditions
- UL Listed for operation remote from the lighting fixture

Fonctions

- Integral 1" threaded nipple with locknut facilitates hook-up to electrical conduit or to the mounting bracket when used on a pole

Application


- Billboard, road sign lighting, and some outdoor sports facilities, such as tennis courts

Outdoor Weatherproof (79W)

Versions



Schéma dimensionnel



Product	B1	B2	B3	C1	C2
OUTDOOR WEATHERPROOF HID 79W6592001	7,3 in	6,4 in	1 in	11,3 in	1,9 in
OUTDOOR WEATHERPROOF HID 79W6351001	7,3 in	6,4 in	1 in	13,8 in	1,9 in

Fonctionnement et électricité

Fréquence d'entrée 60 Hz

Renseignements généraux

Nombre de lampes 1 piece/unit

Type de lampe MH

Mécanique et boîtier

Boîtier OW

Fonctionnement et électricité

Order Code	Full Product Name	Tension d'entrée
505974	OUTDOOR WEATHERPROOF HID MH BAL 2X400W M59 120/240V WP	120/240 V

Order Code	Full Product Name	Tension d'entrée
399428	OUTDOOR WEATHERPROOF HID MH BAL 1000W M47 QUAD WP	120/208/240/277 V

Outdoor Weatherproof (79W)

