



Sleek design, maximum performance

Postline (74P)

Lantern-type, post-top fixtures mounted on slender poles often require ballasts which fit in the poles. Postline ballasts include a special, elongated core and coil ballast encased and potted in a high temperature resin (Class H, 180°C max.) in cylindrical housings of a diameter to accommodate being placed within a 3" or 4" diameter pole.

Benefits

- Conveniently fits inside a 3" or 4" diameter pole

Features

- Capacitor and ignitor (where required) are included within the can
- Includes leads necessary for direct connection to a photocell
- A 1/2" threaded nipple is provided for verticle mounting
- Leads extend from both ends of the can for ease of installation

Application

- Post top luminaires


Postline (74P)

Versions



74P5104011P

Dimensional drawing



Product	B3	C1
POSTLINE HID 74P8104011P	2.55 in	17.6 in
POSTLINE HID 74P8013011P	2.55 in	21 in
POSTLINE HID 74P7703011P	2.55 in	7 in
POSTLINE HID 74P7903011P	2.55 in	12 in

Operating and Electrical	
Input Frequency	60 Hz
General Information	
Number Of Lamps	1 piece/unit
Lamp Type	HPS
Mechanical and Housing	
Housing	74P

Operating and Electrical

Order Code	Full Product Name	Input Voltage
194084	POSTLINE HID HPS BAL 35W S76 120V POSTLINE	120 V
190108	POSTLINE HID HPS BAL 70W S62 120V POSTLINE	120 V

Order Code	Full Product Name	Input Voltage
194167	POSTLINE HID HPS BAL 100W S54 208V POSTLINE	208 V
194175	POSTLINE HID HPS BAL 150W S55 120V POSTLINE	120 V

