



Sleek design, maximum performance

Postline (74P)

Lantern-type, post-top fixtures mounted on slender poles often require ballasts which fit in the poles. Postline ballasts include a special, elongated core and coil ballast encased and potted in a high temperature resin (Class H, 180°C max.) in cylindrical housings of a diameter to accommodate being placed within a 3" or 4" diameter pole.

Avantages

- Conveniently fits inside a 3" or 4" diameter pole

Fonctions

- Capacitor and ignitor (where required) are included within the can
- Includes leads necessary for direct connection to a photocell
- A 1/2" threaded nipple is provided for verticle mounting
- Leads extend from both ends of the can for ease of installation

Application


- Post top luminaires

Postline (74P)

Versions



Schéma dimensionnel



Product	B3	C1
POSTLINE HID 74P8104011P	2,55 in	17,6 in
POSTLINE HID 74P8013011P	2,55 in	21 in
POSTLINE HID 74P7703011P	2,55 in	7 in
POSTLINE HID 74P7903011P	2,55 in	12 in

Fonctionnement et électricité

Fréquence d'entrée 60 Hz

Renseignements généraux

Nombre de lampes 1 piece/unit

Type de lampe HPS

Mécanique et boîtier

Boîtier 74P

Fonctionnement et électricité

Order Code	Full Product Name	Tension d'entrée
194084	POSTLINE HID HPS BAL 35W S76 120V POSTLINE	120 V
190108	POSTLINE HID HPS BAL 70W S62 120V POSTLINE	120 V

Order Code	Full Product Name	Tension d'entrée
194167	POSTLINE HID HPS BAL 100W S54 208V POSTLINE	208 V
194175	POSTLINE HID HPS BAL 150W S55 120V POSTLINE	120 V

