



# CoreLine Waterproof – the clear choice for LED

## CoreLine Waterproof

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Waterproof range of LED products can be used to replace traditional waterproof luminaires with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch.

### Benefits

- Up to 50% energy savings compared with TL-D
- Reliable LED technology – maintenance-free
- Direct replacement for conventional waterproof luminaires in terms of light performance, installation flexibility and length

### Features

- Reliable integrated LED technology, ensuring maintenance-free installation and a long lifetime
- Can be used to replace traditional waterproof luminaires ranging from 18 to 58 W TL-D
- Wide-beam light distribution
- Diffuser with optical element ensures visual comfort
- Ceiling-mounted bracket and suspension hooks included; installation can be made vandal-proof by additional screw fixation of mounting brackets

### Application




- Parking garages
- Warehouses
- General lighting

# CoreLine Waterproof

## Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

## Dimensional drawing



## Product details



CoreLine Waterproof WT120C G2  
PCU-7DPP



CoreLine Waterproof WT120C G2  
PCU-3DPP



CoreLine Waterproof WT120C G2  
PCU-10DPP




CoreLine Waterproof WT120C G2  
PCU-9DPP

# CoreLine Waterproof


## Product details



CoreLine Waterproof WT120C G2  
PCU-12DPP



CoreLine waterproof G2 (WT120C  
G2),MDU, Motion Detection Unit




CoreLine Waterproof WT120C G2  
PCU-2DPP



CoreLine Waterproof WT120C G2  
PCU-13DPP



CoreLine Waterproof WT120C G2  
PCU-8DPP



CoreLine waterproof G2 (WT120C  
G2),MDU, Motion Detection Unit



CoreLine Waterproof WT120C G2  
PCU-11DPP



CoreLine waterproof G2 (WT120C  
G2),Emergency lighting, TrustSight

# CoreLine Waterproof

## General Information

CE mark	CE mark
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on easily flammable surfaces
Glow-wire test	Temperature 850 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit

## Light Technical

Color rendering index (CRI)	>80
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	1.6

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz

## Mechanical and Housing

Housing Color	Gray
---------------	------

## Approval and Application

Protection class IEC	Safety class I
Mech. impact protection code	IK08
Ingress protection code	IP65

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

## General Information (1/2)

Order Code	Full Product Name	Type of emergency lighting battery	Lamp family code	Embedded control	Product family code
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	-	LED27S	-	WT130C
96248700	WT120C G2 LED27S/840 PSU MDU L1200	-	LED27S	Movement and light sensor (On/Off)	WT130C
96249400	WT120C G2 LED27S/840 PSU MDU TW3 L1200	-	LED27S	Movement and light sensor (On/Off)	WT130C
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	Lithium	LED27S	-	WT130C
88307500	WT120C G2 LED27S/840 PSD L1200	-	LED27S	-	WT130C
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	Lithium	LED27S	-	WT130C
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	-	LED40S	-	WT130C
96257900	WT120C G2 LED40S/840 PSU MDU TW3 L1200	-	LED40S	Movement and light sensor (On/Off)	WT130C
16316700	WT120C G2 LED40S/840 PSU WEC L1200	-	LED40S	-	WT130C
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-	LED40S	-	WT130C
88309900	WT120C G2 LED40S/840 PSD L1200	-	LED40S	-	WT130C
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	Lithium	LED40S	-	WT130C
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	Lithium	LED40S	Movement and light sensor (On/Off)	WT130C
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	Lithium	LED40S	-	WT130C
84046600	WT120C G2 LED27S/840 PSU L1200	-	-	-	-
84048000	WT120C G2 LED40S/840 PSU L1200	-	-	-	-
36933499	WT120C G2 LED40S/865 PSU L1200	-	-	-	-
34976399	WT120C G2 LED18S/840 PSU PCO L600	-	-	-	-
34977099	WT120C G2 LED25S/840 PSU PCO L1200	-	-	-	-
34978799	WT120C G2 LED31S/840 PSU PCO L1500	-	-	-	-
34979499	WT120C G2 LED37S/840 PSU PCO L1200	-	-	-	-
34980099	WT120C G2 LED57S/840 PSU PCO L1500	-	-	-	-

Order Code	Full Product Name	Type of emergency lighting battery	Lamp family code	Embedded control	Product family code
34981799	WT120C G2 LED75S/840 PSU PCO L1500	-	-	-	-
96244900	WT120C G2 LED19S/840 PSU MDU L600	-	LED27S	Movement and light sensor (On/Off)	WT130C
88306800	WT120C G2 LED19S/840 PSD L600	-	LED19S	-	WT130C
84045900	WT120C G2 LED19S/840 PSU L600	-	-	-	-
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	-	LED34S	-	WT130C
96267800	WT120C G2 LED34S/840 PSU MDU L1500	-	LED34S	Movement and light sensor (On/Off)	WT130C
96268500	WT120C G2 LED34S/840 PSU MDU TW3 L1500	-	LED34S	Movement and light sensor (On/Off)	WT130C
88308200	WT120C G2 LED34S/840 PSD L1500	-	LED34S	-	WT130C
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	Lithium	LED34S	-	WT130C
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	Lithium	LED34S	Movement and light sensor (On/Off)	WT130C
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	Lithium	LED34S	-	WT130C
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	-	LED60S	-	WT130C
96275300	WT120C G2 LED60S/840 PSU MDU L1500	-	LED60S	Movement and light sensor (On/Off)	WT130C
96276000	WT120C G2 LED60S/840 PSU MDU TW3 L1500	-	LED60S	Movement and light sensor (On/Off)	WT130C
16318100	WT120C G2 LED60S/840 PSU WEC L1500	-	LED60S	-	WT130C
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	-	LED60S	-	WT130C
88310500	WT120C G2 LED60S/840 PSD L1500	-	LED60S	-	WT130C
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	Lithium	LED60S	-	WT130C
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	Lithium	LED60S	Movement and light sensor (On/Off)	WT130C
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	Lithium	LED60S	-	WT130C
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	-	LED80S	-	WT130C

Order Code	Full Product Name	Type of emergency lighting battery	Lamp family code	Embedded control	Product family code
96286900	WT120C G2 LED80S/840 PSU MDU L1500	-	LED80S	Movement and light sensor (On/Off)	WT130C
40929600	WT120C G2 LED80S/840 PSD L1500	-	LED80S	-	WT130C
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	Lithium	LED80S	-	WT130C
97578400	WT120C G2 LED65S/840 WIA L1500	-	-	-	WT130C
84047300	WT120C G2 LED34S/840 PSU L1500	-	-	-	-
84049700	WT120C G2 LED60S/840 PSU L1500	-	-	-	-
40928900	WT120C G2 LED80S/840 PSU L1500	-	-	-	-
36934199	WT120C G2 LED34S/865 PSU L1500	-	-	-	-
36935899	WT120C G2 LED60S/865 PSU L1500	-	-	-	-

## General Information (2/2)

Order Code	Full Product Name	Service tag	Order Code	Full Product Name	Service tag
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	Yes	91686500	WT120C G2 LED34S/840 PSU TW3 L1500	Yes
96248700	WT120C G2 LED27S/840 PSU MDU L1200	Yes	96267800	WT120C G2 LED34S/840 PSU MDU L1500	Yes
96249400	WT120C G2 LED27S/840 PSU MDU TW3 L1200	Yes	96268500	WT120C G2 LED34S/840 PSU MDU TW3 L1500	Yes
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	Yes	88308200	WT120C G2 LED34S/840 PSD L1500	Yes
88307500	WT120C G2 LED27S/840 PSD L1200	Yes	85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	Yes
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	Yes	96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	Yes
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	Yes	88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	Yes
96257900	WT120C G2 LED40S/840 PSU MDU TW3 L1200	Yes	91688900	WT120C G2 LED60S/840 PSU TW3 L1500	Yes
16316700	WT120C G2 LED40S/840 PSU WEC L1200	Yes	96275300	WT120C G2 LED60S/840 PSU MDU L1500	Yes
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	Yes	96276000	WT120C G2 LED60S/840 PSU MDU TW3 L1500	Yes
88309900	WT120C G2 LED40S/840 PSD L1200	Yes	16318100	WT120C G2 LED60S/840 PSU WEC L1500	Yes
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	Yes	16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	Yes
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	Yes	88310500	WT120C G2 LED60S/840 PSD L1500	Yes
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	Yes	85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	Yes
84046600	WT120C G2 LED27S/840 PSU L1200	Yes	96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	Yes
84048000	WT120C G2 LED40S/840 PSU L1200	Yes	88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	Yes
36933499	WT120C G2 LED40S/865 PSU L1200	-	40930200	WT120C G2 LED80S/840 PSU TW3 L1500	Yes
34976399	WT120C G2 LED18S/840 PSU PCO L600	Yes	96286900	WT120C G2 LED80S/840 PSU MDU L1500	Yes
34977099	WT120C G2 LED25S/840 PSU PCO L1200	Yes	40929600	WT120C G2 LED80S/840 PSD L1500	Yes
34978799	WT120C G2 LED31S/840 PSU PCO L1500	Yes	40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	Yes
34979499	WT120C G2 LED37S/840 PSU PCO L1200	Yes	97578400	WT120C G2 LED65S/840 WIA L1500	-
34980099	WT120C G2 LED57S/840 PSU PCO L1500	Yes	84047300	WT120C G2 LED34S/840 PSU L1500	Yes
34981799	WT120C G2 LED75S/840 PSU PCO L1500	Yes	84049700	WT120C G2 LED60S/840 PSU L1500	Yes
96244900	WT120C G2 LED19S/840 PSU MDU L600	Yes	40928900	WT120C G2 LED80S/840 PSU L1500	Yes
88306800	WT120C G2 LED19S/840 PSD L600	Yes	36934199	WT120C G2 LED34S/865 PSU L1500	-
84045900	WT120C G2 LED19S/840 PSU L600	Yes	36935899	WT120C G2 LED60S/865 PSU L1500	-

# CoreLine Waterproof

## Light Technical

Order Code	Full Product Name	Correlated		Luminous Flux	Optic type
		Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)		
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	4000 K	126 lm/W	2,700 lm	Wide beam
96248700	WT120C G2 LED27S/840 PSU MDU L1200	4000 K	123 lm/W	2,700 lm	Wide beam
96249400	WT120C G2 LED27S/840 PSU MDU TW3 L1200	4000 K	123 lm/W	2,700 lm	Wide beam
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	4000 K	104 lm/W	2,700 lm	Wide beam
88307500	WT120C G2 LED27S/840 PSD L1200	4000 K	123 lm/W	2,700 lm	Wide beam
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	4000 K	100 lm/W	2,700 lm	Wide beam
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	4000 K	133 lm/W	4,000 lm	Wide beam
96257900	WT120C G2 LED40S/840 PSU MDU TW3 L1200	4000 K	133 lm/W	4,000 lm	Wide beam
16316700	WT120C G2 LED40S/840 PSU WEC L1200	4000 K	138 lm/W	4,000 lm	Wide beam
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	4000 K	136 lm/W	4,000 lm	Wide beam
88309900	WT120C G2 LED40S/840 PSD L1200	4000 K	131 lm/W	4,000 lm	Wide beam
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	4000 K	121 lm/W	4,000 lm	Wide beam
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	4000 K	114 lm/W	4,000 lm	Wide beam
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	4000 K	113 lm/W	4,000 lm	Wide beam
84046600	WT120C G2 LED27S/840 PSU L1200	4000 K	132 lm/W	2,700 lm	Wide beam
84048000	WT120C G2 LED40S/840 PSU L1200	4000 K	140 lm/W	4,000 lm	Wide beam

Order Code	Full Product Name	Correlated		Luminous Flux	Optic type
		Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)		
36933499	WT120C G2 LED40S/865 PSU L1200	6500 K	140 lm/W	4,000 lm	Wide beam
34976399	WT120C G2 LED18S/840 PSU PCO L600	4000 K	121 lm/W	1,800 lm	Very wide beam
34977099	WT120C G2 LED25S/840 PSU PCO L1200	4000 K	122 lm/W	2,500 lm	Very wide beam
34978799	WT120C G2 LED31S/840 PSU PCO L1500	4000 K	128 lm/W	3,100 lm	Very wide beam
34979499	WT120C G2 LED37S/840 PSU PCO L1200	4000 K	130 lm/W	3,700 lm	Very wide beam
34980099	WT120C G2 LED57S/840 PSU PCO L1500	4000 K	133 lm/W	5,700 lm	Very wide beam
34981799	WT120C G2 LED75S/840 PSU PCO L1500	4000 K	131 lm/W	7,500 lm	Very wide beam
96244900	WT120C G2 LED19S/840 PSU MDU L600	4000 K	116 lm/W	1,900 lm	Wide beam
88306800	WT120C G2 LED19S/840 PSD L600	4000 K	115 lm/W	1,900 lm	Wide beam
84045900	WT120C G2 LED19S/840 PSU L600	4000 K	127 lm/W	1,900 lm	Wide beam
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	4000 K	133 lm/W	3,400 lm	Wide beam
96267800	WT120C G2 LED34S/840 PSU MDU L1500	4000 K	131 lm/W	3,400 lm	Wide beam
96268500	WT120C G2 LED34S/840 PSU MDU TW3 L1500	4000 K	131 lm/W	3,400 lm	Wide beam
88308200	WT120C G2 LED34S/840 PSD L1500	4000 K	131 lm/W	3,400 lm	Wide beam
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	4000 K	113 lm/W	3,400 lm	Wide beam
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	4000 K	110 lm/W	3,400 lm	Wide beam

## CoreLine Waterproof

Order Code	Full Product Name	Correlated Color	Luminous		Optic type
		Temperature (Nom)	Efficacy (rated) (Nom)	Luminous Flux	
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	4000 K	110 lm/W	3,400 lm	Wide beam
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	4000 K	135 lm/W	6,000 lm	Wide beam
96275300	WT120C G2 LED60S/840 PSU MDU L1500	4000 K	133 lm/W	6,000 lm	Wide beam
96276000	WT120C G2 LED60S/840 PSU MDU TW3 L1500	4000 K	133 lm/W	6,000 lm	Wide beam
16318100	WT120C G2 LED60S/840 PSU WEC L1500	4000 K	135 lm/W	6,000 lm	Wide beam
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	4000 K	136 lm/W	6,000 lm	Wide beam
88310500	WT120C G2 LED60S/840 PSD L1500	4000 K	133 lm/W	6,000 lm	Wide beam
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	4000 K	121 lm/W	6,000 lm	Wide beam
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	4000 K	120 lm/W	6,000 lm	Wide beam
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	4000 K	121 lm/W	6,000 lm	Wide beam

Order Code	Full Product Name	Correlated Color	Luminous		Optic type
		Temperature (Nom)	Efficacy (rated) (Nom)	Luminous Flux	
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	4000 K	133 lm/W	8,000 lm	Wide beam
96286900	WT120C G2 LED80S/840 PSU MDU L1500	4000 K	131 lm/W	8,000 lm	Wide beam
40929600	WT120C G2 LED80S/840 PSD L1500	4000 K	129 lm/W	8,000 lm	Wide beam
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	4000 K	126 lm/W	8,000 lm	Wide beam
97578400	WT120C G2 LED65S/840 WIA L1500	4000 K	144 lm/W	6,500 lm	Wide beam
84047300	WT120C G2 LED34S/840 PSU L1500	4000 K	140 lm/W	3,400 lm	Wide beam
84049700	WT120C G2 LED60S/840 PSU L1500	4000 K	140 lm/W	6,000 lm	Wide beam
40928900	WT120C G2 LED80S/840 PSU L1500	4000 K	140 lm/W	8,000 lm	Wide beam
36934199	WT120C G2 LED34S/865 PSU L1500	6500 K	139 lm/W	3,400 lm	Wide beam
36935899	WT120C G2 LED60S/865 PSU L1500	6500 K	140 lm/W	6,000 lm	Wide beam

### Operating and Electrical

Order Code	Full Product Name	Power Consumption
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	21.5 W
96248700	WT120C G2 LED27S/840 PSU MDU L1200	22 W
96249400	WT120C G2 LED27S/840 PSU MDU TW3 L1200	22 W
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	26 W
88307500	WT120C G2 LED27S/840 PSD L1200	22 W
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	27 W
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	30 W
96257900	WT120C G2 LED40S/840 PSU MDU TW3 L1200	30 W
16316700	WT120C G2 LED40S/840 PSU WEC L1200	29 W
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	29.5 W
88309900	WT120C G2 LED40S/840 PSD L1200	30.5 W
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	33 W
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	35 W
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	35.5 W
84046600	WT120C G2 LED27S/840 PSU L1200	20.5 W

Order Code	Full Product Name	Power Consumption
84048000	WT120C G2 LED40S/840 PSU L1200	28.6 W
36933499	WT120C G2 LED40S/865 PSU L1200	28.5 W
34976399	WT120C G2 LED18S/840 PSU PCO L600	15 W
34977099	WT120C G2 LED25S/840 PSU PCO L1200	20.5 W
34978799	WT120C G2 LED31S/840 PSU PCO L1500	24.3 W
34979499	WT120C G2 LED37S/840 PSU PCO L1200	28.6 W
34980099	WT120C G2 LED57S/840 PSU PCO L1500	42.9 W
34981799	WT120C G2 LED75S/840 PSU PCO L1500	57.1 W
96244900	WT120C G2 LED19S/840 PSU MDU L600	16.4 W
88306800	WT120C G2 LED19S/840 PSD L600	16.5 W
84045900	WT120C G2 LED19S/840 PSU L600	15 W
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	25.5 W
96267800	WT120C G2 LED34S/840 PSU MDU L1500	26 W
96268500	WT120C G2 LED34S/840 PSU MDU TW3 L1500	26 W
88308200	WT120C G2 LED34S/840 PSD L1500	26 W



## CoreLine Waterproof

Order Code	Full Product Name	Power Consumption
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	30 W
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	31 W
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	31 W
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	44.5 W
96275300	WT120C G2 LED60S/840 PSU MDU L1500	45 W
96276000	WT120C G2 LED60S/840 PSU MDU TW3 L1500	45 W
16318100	WT120C G2 LED60S/840 PSU WEC L1500	44.5 W
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	44 W
88310500	WT120C G2 LED60S/840 PSD L1500	45 W
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	49.5 W
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	50 W

Order Code	Full Product Name	Power Consumption
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	49.5 W
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	60 W
96286900	WT120C G2 LED80S/840 PSU MDU L1500	61 W
40929600	WT120C G2 LED80S/840 PSD L1500	62 W
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	63.5 W
97578400	WT120C G2 LED65S/840 WIA L1500	45 W
84047300	WT120C G2 LED34S/840 PSU L1500	24.3 W
84049700	WT120C G2 LED60S/840 PSU L1500	42.9 W
40928900	WT120C G2 LED80S/840 PSU L1500	57.1 W
36934199	WT120C G2 LED34S/865 PSU L1500	24.5 W
36935899	WT120C G2 LED60S/865 PSU L1500	43 W

### Temperature

Order Code	Full Product Name	Ambient temperature range
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	-20 to +35 °C
96248700	WT120C G2 LED27S/840 PSU MDU L1200	-20 to +35 °C
96249400	WT120C G2 LED27S/840 PSU MDU TW3 L1200	-20 to +35 °C
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	0 to +25 °C
88307500	WT120C G2 LED27S/840 PSD L1200	-20 to +35 °C
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	0 to +25 °C
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	-20 to +35 °C
96257900	WT120C G2 LED40S/840 PSU MDU TW3 L1200	-20 to +35 °C
16316700	WT120C G2 LED40S/840 PSU WEC L1200	-20 to +35 °C
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-20 to +35 °C
88309900	WT120C G2 LED40S/840 PSD L1200	-20 to +35 °C
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	0 to +25 °C
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	0 to +25 °C
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	0 to +25 °C
84046600	WT120C G2 LED27S/840 PSU L1200	-20 to +40 °C
84048000	WT120C G2 LED40S/840 PSU L1200	-20 to +40 °C
36933499	WT120C G2 LED40S/865 PSU L1200	-20 to +40 °C
34976399	WT120C G2 LED18S/840 PSU PCO L600	-20 to +40 °C
34977099	WT120C G2 LED25S/840 PSU PCO L1200	-20 to +40 °C
34978799	WT120C G2 LED31S/840 PSU PCO L1500	-20 to +40 °C
34979499	WT120C G2 LED37S/840 PSU PCO L1200	-20 to +40 °C
34980099	WT120C G2 LED57S/840 PSU PCO L1500	-20 to +40 °C
34981799	WT120C G2 LED75S/840 PSU PCO L1500	-20 to +40 °C
96244900	WT120C G2 LED19S/840 PSU MDU L600	-20 to +35 °C
88306800	WT120C G2 LED19S/840 PSD L600	-20 to +35 °C
84045900	WT120C G2 LED19S/840 PSU L600	-20 to +40 °C
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	-20 to +35 °C

Order Code	Full Product Name	Ambient temperature range
96267800	WT120C G2 LED34S/840 PSU MDU L1500	-20 to +35 °C
96268500	WT120C G2 LED34S/840 PSU MDU TW3 L1500	-20 to +35 °C
88308200	WT120C G2 LED34S/840 PSD L1500	-20 to +35 °C
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	0 to +25 °C
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	0 to +25 °C
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	0 to +25 °C
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	-20 to +35 °C
96275300	WT120C G2 LED60S/840 PSU MDU L1500	-20 to +35 °C
96276000	WT120C G2 LED60S/840 PSU MDU TW3 L1500	-20 to +35 °C
16318100	WT120C G2 LED60S/840 PSU WEC L1500	-20 to +35 °C
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	-20 to +35 °C
88310500	WT120C G2 LED60S/840 PSD L1500	-20 to +35 °C
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	0 to +25 °C
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	0 to +25 °C
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	0 to +25 °C
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	-20 to +35 °C
96286900	WT120C G2 LED80S/840 PSU MDU L1500	-20 to +35 °C
40929600	WT120C G2 LED80S/840 PSD L1500	-20 to +35 °C
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	0 to +25 °C
97578400	WT120C G2 LED65S/840 WIA L1500	-20 to +35 °C
84047300	WT120C G2 LED34S/840 PSU L1500	-20 to +40 °C
84049700	WT120C G2 LED60S/840 PSU L1500	-20 to +40 °C
40928900	WT120C G2 LED80S/840 PSU L1500	-20 to +40 °C
36934199	WT120C G2 LED34S/865 PSU L1500	-20 to +40 °C
36935899	WT120C G2 LED60S/865 PSU L1500	-20 to +40 °C

### Controls and Dimming

Order Code	Full Product Name	Dimmable
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	No

Order Code	Full Product Name	Dimmable
96248700	WT120C G2 LED27S/840 PSU MDU L1200	No

## CoreLine Waterproof

Order Code	Full Product Name	Dimmable
96249400	WT120C G2 LED275/840 PSU MDU TW3 L1200	No
85418000	WT120C G2 LED275/840 PSU ELB3 L1200	No
88307500	WT120C G2 LED275/840 PSD L1200	Yes
88311200	WT120C G2 LED275/840 PSD ELB3 L1200	Yes
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	No
96257900	WT120C G2 LED40S/840 PSU MDU TW3 L1200	No
16316700	WT120C G2 LED40S/840 PSU WEC L1200	No
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	No
88309900	WT120C G2 LED40S/840 PSD L1200	Yes
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	No
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	No
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	Yes
84046600	WT120C G2 LED275/840 PSU L1200	No
84048000	WT120C G2 LED40S/840 PSU L1200	No
36933499	WT120C G2 LED40S/865 PSU L1200	No
34976399	WT120C G2 LED18S/840 PSU PCO L600	No
34977099	WT120C G2 LED25S/840 PSU PCO L1200	No
34978799	WT120C G2 LED31S/840 PSU PCO L1500	No
34979499	WT120C G2 LED37S/840 PSU PCO L1200	No
34980099	WT120C G2 LED57S/840 PSU PCO L1500	No
34981799	WT120C G2 LED75S/840 PSU PCO L1500	No
96244900	WT120C G2 LED19S/840 PSU MDU L600	No
88306800	WT120C G2 LED19S/840 PSD L600	Yes
84045900	WT120C G2 LED19S/840 PSU L600	No
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	No

Order Code	Full Product Name	Dimmable
96267800	WT120C G2 LED34S/840 PSU MDU L1500	No
96268500	WT120C G2 LED34S/840 PSU MDU TW3 L1500	No
88308200	WT120C G2 LED34S/840 PSD L1500	Yes
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	No
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	No
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	Yes
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	No
96275300	WT120C G2 LED60S/840 PSU MDU L1500	No
96276000	WT120C G2 LED60S/840 PSU MDU TW3 L1500	No
16318100	WT120C G2 LED60S/840 PSU WEC L1500	No
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	No
88310500	WT120C G2 LED60S/840 PSD L1500	Yes
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	No
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	No
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	Yes
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	No
96286900	WT120C G2 LED80S/840 PSU MDU L1500	No
40929600	WT120C G2 LED80S/840 PSD L1500	Yes
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	No
97578400	WT120C G2 LED65S/840 WIA L1500	Yes
84047300	WT120C G2 LED34S/840 PSU L1500	No
84049700	WT120C G2 LED60S/840 PSU L1500	No
40928900	WT120C G2 LED80S/840 PSU L1500	No
36934199	WT120C G2 LED34S/865 PSU L1500	No
36935899	WT120C G2 LED60S/865 PSU L1500	No

### Emergency Operation

Order Code	Full Product Name	Emergency flux	Power consumption during Central DC emergency mode
91685800	WT120C G2 LED275/840 PSU TW3 L1200	-	-
96248700	WT120C G2 LED275/840 PSU MDU L1200	-	-
96249400	WT120C G2 LED275/840 PSU MDU TW3 L1200	-	-
85418000	WT120C G2 LED275/840 PSU ELB3 L1200	500 lm	3 W
88307500	WT120C G2 LED275/840 PSD L1200	-	-
88311200	WT120C G2 LED275/840 PSD ELB3 L1200	500 lm	3 W
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	-	-
96257900	WT120C G2 LED40S/840 PSU MDU TW3 L1200	-	-
16316700	WT120C G2 LED40S/840 PSU WEC L1200	-	-
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	-	-
88309900	WT120C G2 LED40S/840 PSD L1200	-	-

Order Code	Full Product Name	Emergency flux	Power consumption during Central DC emergency mode
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	500 lm	3 W
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	500 lm	3 W
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	500 lm	3 W
84046600	WT120C G2 LED275/840 PSU L1200	-	-
84048000	WT120C G2 LED40S/840 PSU L1200	-	-
36933499	WT120C G2 LED40S/865 PSU L1200	-	-
34976399	WT120C G2 LED18S/840 PSU PCO L600	-	-
34977099	WT120C G2 LED25S/840 PSU PCO L1200	-	-
34978799	WT120C G2 LED31S/840 PSU PCO L1500	-	-
34979499	WT120C G2 LED37S/840 PSU PCO L1200	-	-
34980099	WT120C G2 LED57S/840 PSU PCO L1500	-	-

# CoreLine Waterproof

Order Code	Full Product Name	Emergency flux	Power consumption during Central DC emergency mode
34981799	WT120C G2 LED75S/840 PSU PCO L1500	-	-
96244900	WT120C G2 LED19S/840 PSU MDU L600	-	-
88306800	WT120C G2 LED19S/840 PSD L600	-	-
84045900	WT120C G2 LED19S/840 PSU L600	-	-
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	-	-
96267800	WT120C G2 LED34S/840 PSU MDU L1500	-	-
96268500	WT120C G2 LED34S/840 PSU MDU TW3 L1500	-	-
88308200	WT120C G2 LED34S/840 PSD L1500	-	-
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	500 lm	3 W
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	500 lm	3 W
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	500 lm	3 W
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	-	-
96275300	WT120C G2 LED60S/840 PSU MDU L1500	-	-
96276000	WT120C G2 LED60S/840 PSU MDU TW3 L1500	-	-

Order Code	Full Product Name	Emergency flux	Power consumption during Central DC emergency mode
16318100	WT120C G2 LED60S/840 PSU WEC L1500	-	-
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	-	-
88310500	WT120C G2 LED60S/840 PSD L1500	-	-
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	500 lm	3 W
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	500 lm	3 W
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	500 lm	3 W
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	-	-
96286900	WT120C G2 LED80S/840 PSU MDU L1500	-	-
40929600	WT120C G2 LED80S/840 PSD L1500	-	-
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	500 lm	3 W
97578400	WT120C G2 LED65S/840 WIA L1500	-	-
84047300	WT120C G2 LED34S/840 PSU L1500	-	-
84049700	WT120C G2 LED60S/840 PSU L1500	-	-
40928900	WT120C G2 LED80S/840 PSU L1500	-	-
36934199	WT120C G2 LED34S/865 PSU L1500	-	-
36935899	WT120C G2 LED60S/865 PSU L1500	-	-

## Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	(0.38,0.38)SDCM<=3
96248700	WT120C G2 LED27S/840 PSU MDU L1200	(0.38,0.38)SDCM<=3
96249400	WT120C G2 LED27S/840 PSU MDU TW3 L1200	(0.38,0.38)SDCM<=3
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	(0.38,0.38)SDCM<=3
88307500	WT120C G2 LED27S/840 PSD L1200	(0.38,0.38)SDCM<=3
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	(0.38,0.38)SDCM<=3
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	(0.38,0.38)SDCM<=3
96257900	WT120C G2 LED40S/840 PSU MDU TW3 L1200	(0.38,0.38)SDCM<=3
16316700	WT120C G2 LED40S/840 PSU WEC L1200	(0.38,0.38)SDCM<=3
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	(0.38,0.38)SDCM<=3
88309900	WT120C G2 LED40S/840 PSD L1200	(0.38,0.38)SDCM<=3
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	(0.38,0.38)SDCM<=3
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	(0.38,0.38)SDCM<=3
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	(0.38,0.38)SDCM<=3
84046600	WT120C G2 LED27S/840 PSU L1200	(0.38,0.38)SDCM<=3
84048000	WT120C G2 LED40S/840 PSU L1200	(0.38,0.38)SDCM<=3
36933499	WT120C G2 LED40S/865 PSU L1200	(0.31,0.32)SDCM<=3
34976399	WT120C G2 LED18S/840 PSU PCO L600	(0.38,0.38)SDCM<=3
34977099	WT120C G2 LED25S/840 PSU PCO L1200	(0.38,0.38)SDCM<=3
34978799	WT120C G2 LED31S/840 PSU PCO L1500	(0.38,0.38)SDCM<=3

Order Code	Full Product Name	Initial chromaticity
34979499	WT120C G2 LED37S/840 PSU PCO L1200	(0.38,0.38)SDCM<=3
34980099	WT120C G2 LED57S/840 PSU PCO L1500	(0.38,0.38)SDCM<=3
34981799	WT120C G2 LED75S/840 PSU PCO L1500	(0.38,0.38)SDCM<=3
96244900	WT120C G2 LED19S/840 PSU MDU L600	(0.38,0.38)SDCM<=3
88306800	WT120C G2 LED19S/840 PSD L600	(0.38,0.38)SDCM<=3
84045900	WT120C G2 LED19S/840 PSU L600	(0.38,0.38)SDCM<=3
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	(0.38,0.38)SDCM<=3
96267800	WT120C G2 LED34S/840 PSU MDU L1500	(0.38,0.38)SDCM<=3
96268500	WT120C G2 LED34S/840 PSU MDU TW3 L1500	(0.38,0.38)SDCM<=3
88308200	WT120C G2 LED34S/840 PSD L1500	(0.38,0.38)SDCM<=3
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	(0.38,0.38)SDCM<=3
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	(0.38,0.38)SDCM<=3
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	(0.38,0.38)SDCM<=3
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	(0.38,0.38)SDCM<=3
96275300	WT120C G2 LED60S/840 PSU MDU L1500	(0.38,0.38)SDCM<=3
96276000	WT120C G2 LED60S/840 PSU MDU TW3 L1500	(0.38,0.38)SDCM<=3
16318100	WT120C G2 LED60S/840 PSU WEC L1500	(0.38,0.38)SDCM<=3
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	(0.38,0.38)SDCM<=3
88310500	WT120C G2 LED60S/840 PSD L1500	(0.38,0.38)SDCM<=3
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	(0.38,0.38)SDCM<=3

# CoreLine Waterproof

Order Code	Full Product Name	Initial chromaticity
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	(0.38,0.38)SDCM<=3
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	(0.38,0.38)SDCM<=3
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	(0.38,0.38)SDCM<=3
96286900	WT120C G2 LED80S/840 PSU MDU L1500	(0.38,0.38)SDCM<=3
40929600	WT120C G2 LED80S/840 PSD L1500	(0.38,0.38)SDCM<=3
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	(0.38,0.38)SDCM<=3

Order Code	Full Product Name	Initial chromaticity
97578400	WT120C G2 LED65S/840 WIA L1500	(0.38,0.38)SDCM<=3
84047300	WT120C G2 LED34S/840 PSU L1500	(0.38,0.38)SDCM<=3
84049700	WT120C G2 LED60S/840 PSU L1500	(0.38,0.38)SDCM<=3
40928900	WT120C G2 LED80S/840 PSU L1500	(0.38,0.38)SDCM<=3
36934199	WT120C G2 LED34S/865 PSU L1500	(0.31,0.32)SDCM<=3
36935899	WT120C G2 LED60S/865 PSU L1500	(0.31,0.32)SDCM<=3

## Application Conditions

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
91685800	WT120C G2 LED27S/840 PSU TW3 L1200	Not applicable	Not applicable
96248700	WT120C G2 LED27S/840 PSU MDU L1200	Not applicable	Yes
96249400	WT120C G2 LED27S/840 PSU MDU TW3 L1200	Not applicable	Yes
85418000	WT120C G2 LED27S/840 PSU ELB3 L1200	Not applicable	Not applicable
88307500	WT120C G2 LED27S/840 PSD L1200	1%	Not applicable
88311200	WT120C G2 LED27S/840 PSD ELB3 L1200	1%	Not applicable
91687200	WT120C G2 LED40S/840 PSU TW3 L1200	Not applicable	Not applicable
96257900	WT120C G2 LED40S/840 PSU MDU TW3 L1200	Not applicable	Yes
16316700	WT120C G2 LED40S/840 PSU WEC L1200	Not applicable	Not applicable
16317400	WT120C G2 LED40S/840 PSU TW1 WEC L1200	Not applicable	Not applicable
88309900	WT120C G2 LED40S/840 PSD L1200	1%	Not applicable
85419700	WT120C G2 LED40S/840 PSU ELB3 L1200	Not applicable	Not applicable
96263000	WT120C G2 LED40S/840 PSU MDU ELB3 L1200	Not applicable	Yes
88312900	WT120C G2 LED40S/840 PSD ELB3 L1200	1%	Not applicable
84046600	WT120C G2 LED27S/840 PSU L1200	Not applicable	Not applicable
84048000	WT120C G2 LED40S/840 PSU L1200	Not applicable	Not applicable
36933499	WT120C G2 LED40S/865 PSU L1200	Not applicable	Not applicable
34976399	WT120C G2 LED18S/840 PSU PCO L600	Not applicable	Not applicable
34977099	WT120C G2 LED25S/840 PSU PCO L1200	Not applicable	Not applicable
34978799	WT120C G2 LED31S/840 PSU PCO L1500	Not applicable	Not applicable
34979499	WT120C G2 LED37S/840 PSU PCO L1200	Not applicable	Not applicable
34980099	WT120C G2 LED57S/840 PSU PCO L1500	Not applicable	Not applicable

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
34981799	WT120C G2 LED75S/840 PSU PCO L1500	Not applicable	Not applicable
96244900	WT120C G2 LED19S/840 PSU MDU L600	Not applicable	Yes
88306800	WT120C G2 LED19S/840 PSD L600	1%	Not applicable
84045900	WT120C G2 LED19S/840 PSU L600	Not applicable	Not applicable
91686500	WT120C G2 LED34S/840 PSU TW3 L1500	Not applicable	Not applicable
96267800	WT120C G2 LED34S/840 PSU MDU L1500	Not applicable	Yes
96268500	WT120C G2 LED34S/840 PSU MDU TW3 L1500	Not applicable	Yes
88308200	WT120C G2 LED34S/840 PSD L1500	1%	Not applicable
85420300	WT120C G2 LED34S/840 PSU ELB3 L1500	Not applicable	Not applicable
96271500	WT120C G2 LED34S/840 PSU MDU ELB3 L1500	Not applicable	Yes
88313600	WT120C G2 LED34S/840 PSD ELB3 L1500	1%	Not applicable
91688900	WT120C G2 LED60S/840 PSU TW3 L1500	Not applicable	Not applicable
96275300	WT120C G2 LED60S/840 PSU MDU L1500	Not applicable	Yes
96276000	WT120C G2 LED60S/840 PSU MDU TW3 L1500	Not applicable	Yes
16318100	WT120C G2 LED60S/840 PSU WEC L1500	Not applicable	Not applicable
16319800	WT120C G2 LED60S/840 PSU TW1 WEC L1500	Not applicable	Not applicable
88310500	WT120C G2 LED60S/840 PSD L1500	1%	Not applicable
85421000	WT120C G2 LED60S/840 PSU ELB3 L1500	Not applicable	Not applicable
96282100	WT120C G2 LED60S/840 PSU MDU ELB3 L1500	Not applicable	Yes
88314300	WT120C G2 LED60S/840 PSD ELB3 L1500	1%	Not applicable
40930200	WT120C G2 LED80S/840 PSU TW3 L1500	Not applicable	Not applicable
96286900	WT120C G2 LED80S/840 PSU MDU L1500	Not applicable	Yes

## CoreLine Waterproof

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
40929600	WT120C G2 LED80S/840 PSD L1500	1%	Not applicable
40931900	WT120C G2 LED80S/840 PSU L1500 ELB3	Not applicable	Not applicable
97578400	WT120C G2 LED65S/840 WIA L1500	10%	Not applicable
84047300	WT120C G2 LED34S/840 PSU L1500	Not applicable	Not applicable

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
84049700	WT120C G2 LED60S/840 PSU L1500	Not applicable	Not applicable
40928900	WT120C G2 LED80S/840 PSU L1500	Not applicable	Not applicable
36934199	WT120C G2 LED34S/865 PSU L1500	Not applicable	Not applicable
36935899	WT120C G2 LED60S/865 PSU L1500	Not applicable	Not applicable

