



# CDM short arc reflector lamps – perfect colors, long life

## CDM

The perfect color rendering and long life of these Ceramic Discharge Metal-halide lamps make them ideal for fiber optics lighting systems in shop displays, decorative lighting and swimming pool illumination. They can be mounted in color changing projectors.

### Benefits

- Low cost of ownership
- Perfect colors

### Features

- Long life
- High efficiency
- High color rendering index (Ra 90)

### Application

- Shops
- Side lighting
- Archtainment (e.g. swimming pools)

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050


CDM

Versions



CDM-SA/R 150W

Dimensional drawing



Product	D (max)	X	C (max)
CDM-SA/R 150W/942 UNP/1	95.3 mm	280 mm	106 mm

