



Architectural MSA – double ended night colors

MSD

The high luminous efficacy and optimal lamp filling of the double ended Architectural MSA lamps create high beam intensity and excellent color rendering. While the compact arc of the lamp allows efficient beam control and high intensity. Ideal to illuminate architecture of all types at night.

Avantages

- Flux lumineux élevé
- Intensité de faisceau élevée
- Excellentes couleurs

Fonctions

- Rendement lumineux élevé
- Arc compact
- Remplissage de lampe optimal

Application

- Éclairage architectural dynamique

Mises en garde et sécurité


- Un bris de lampe est très peu susceptible d'influer sur votre santé. Si une lampe se brise, aérez la pièce pendant 30 minutes et retirez les morceaux, de préférence avec des gants. Placez-les dans un sac en plastique scellé et portez-le à votre site de gestion des déchets en vue de son recyclage. Évitez d'utiliser un aspirateur.

Versions



XPPR XDMSA 0003

Schéma dimensionnel



Product	D (max)	O	C (max)
MSA 2500 DE UNP/1	41 mm	25 mm	364 mm

