



MSD Platinum – The power to light your creativity

MSD Platinum (Touring/Stage)

The MSD Platinum lamps open up new levels of creative freedom in entertainment lighting, with powerful, compact and brilliantly intense light. Their compact, lightweight design provides the freedom to create smaller, lighter luminaires – for use at any location on stage. And their short arc, high color temperature and innovative reflector produce a sparkling, high beam intensity for outstanding color reproduction. They also offer long and reliable lifetime, high efficacy and fast replacement times. It all adds up to an intensely exciting creative experience.

Benefits

- High beam intensity
- Freedom to create smaller and lighter fixtures
- High perceived brightness
- A long and reliable performance

Features

- Very short arc
- Compact system
- High correlated color temperature
- Philips Platinum technology

Application

- Events
- Shows/Theater
- Touring/Stage

MSD Platinum (Touring/Stage)

Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



XPPR XDMSD 0003

Dimensional drawing




Product	D (max)	O	C (max)
MSD Platinum 20 RB 1CT/8	58.5 mm	1.2 mm	72 mm

Product	D (max)	T (max)	O	C (max)
MSD Platinum 5 R 1CT/8	51.4 mm	6.8 mm	1.0 mm	57.1 mm

MSD Platinum (Touring/Stage)

Dimensional drawing



Product	D (max)	O	C (max)
MSD Platinum 15 R 1CT/8	58.5 mm	1.3 mm	66.4 mm
MSD Platinum 16 R 1CT/8	58.5 mm	1.3 mm	66.4 mm

General Information

Cap-Base	-
Operating Position	UNIVERSAL

Light Technical

Correlated Color Temperature (Nom)	8000 K
Color rendering index (CRI)	-
Color Code	2

Controls and Dimming

Dimmable	Yes
----------	-----

Light Technical

Order Code	Full Product Name	Luminous Flux (Min)	Luminous Flux
928191605314	MSD Platinum 15 R 1CT/8	11,000 lm	13,500 lm
928195205314	MSD Platinum 16 R 1CT/8	14,300 lm	16,000 lm

Order Code	Full Product Name	Luminous Flux (Min)	Luminous Flux
928190805314	MSD Platinum 5 R 1CT/8	7,100 lm	7,950 lm
928495205314	MSD Platinum 20 RB 1CT/8	-	22,400 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
928191605314	MSD Platinum 15 R 1CT/8	300 W
928195205314	MSD Platinum 16 R 1CT/8	330 W

Order Code	Full Product Name	Power Consumption
928190805314	MSD Platinum 5 R 1CT/8	189 W
928495205314	MSD Platinum 20 RB 1CT/8	470 W

