



MSD Platinum – The power to light your creativity

MSD Platinum (Touring/Stage)

The MSD Platinum lamps open up new levels of creative freedom in entertainment lighting, with powerful, compact and brilliantly intense light. Their compact, lightweight design provides the freedom to create smaller, lighter luminaires – for use at any location on stage. And their short arc, high color temperature and innovative reflector produce a sparkling, high beam intensity for outstanding color reproduction. They also offer long and reliable lifetime, high efficacy and fast replacement times. It all adds up to an intensely exciting creative experience.

Avantages

- High beam intensity
- Freedom to create smaller and lighter fixtures
- High perceived brightness
- A long and reliable performance

Fonctions

- Very short arc
- Compact system
- High correlated color temperature
- Philips Platinum technology

Application

- Événements
- Spectacles et théâtre
- Scène et tournée

MSD Platinum (Touring/Stage)

Mises en garde et sécurité

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Versions



Schéma dimensionnel

D

Product	D (max)	T (max)	O	C (max)
MSD Platinum 5 R 1CT/8	51,4 mm	6,8 mm	1,0 mm	57,1 mm
MSD Platinum 14 R 1CT/8	51,5 mm	6,8 mm	0,95 mm	57,1 mm



Product

MSD Platinum 16 R 1CT/8

MSD Platinum (Touring/Stage)

Schéma dimensionnel

D

Product	D (max)	O	C (max)
MSD Platinum 20 R 1CT/8	58,5 mm	1,2 mm	72 mm

Commandes et gradation

Intensité réglable	Yes
--------------------	-----

Renseignements généraux

Culot	-
Application principale	Stage/Touring
Position de fonctionnement	Universal

Données techniques sur l'éclairage

Code de couleur	2
-----------------	---

Fonctionnement et électricité

Order Code	Full Product Name	Tension (max.)	Tension (min.)	Puissance (nominale) (nom.)
249888	MSD Platinum 5 R 1CT/8	-	-	189 W
261503	MSD Platinum 14 R 1CT/8	-	-	280 W

Order Code	Full Product Name	Tension (max.)	Tension (min.)	Puissance (nominale) (nom.)
293050	MSD Platinum 16 R 1CT/8	-	-	330 W
259184	MSD Platinum 20 R 1CT/8	110 V	85 V	470 W

Renseignements généraux

Order Code	Full Product Name	Durée de vie jusqu'à 50% des défaillances (nom.)	Description du système
249888	MSD Platinum 5 R 1CT/8	3000 h	Reflector-E20.6
261503	MSD Platinum 14 R 1CT/8	2000 h	Reflector-E20.6

Order Code	Full Product Name	Durée de vie jusqu'à 50% des défaillances (nom.)	Description du système
293050	MSD Platinum 16 R 1CT/8	1500 h	Reflector E21.9 TCM
259184	MSD Platinum 20 R 1CT/8	1500 h	Reflector E21.9 TCM

Données techniques sur l'éclairage

Order Code	Full Product Name	Température selon la couleur corrélée (nom.)	Indice de rendu des couleurs (nom.)	Flux lumineux (min.)	Flux lumineux (nom.)
249888	MSD Platinum 5 R 1CT/8	8000 K	-	7100 lm	7950 lm
261503	MSD Platinum 14 R 1CT/8	7800 K	-	-	12350 lm

Order Code	Full Product Name	Température selon la couleur corrélée (nom.)	Indice de rendu des couleurs (nom.)	Flux lumineux (min.)	Flux lumineux (nom.)
293050	MSD Platinum 16 R 1CT/8	8000 K	-	14300 lm	16000 lm
259184	MSD Platinum 20 R 1CT/8	8000 K	-	-	22400 lm

MSD Platinum (Touring/Stage)

