



MSR Gold™ FastFit – easy lamp replacement in seconds

MSR Gold™ FastFit

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Benefits

- Lamp replacement in just seconds, exchangeable with halogen lamp
- High beam intensity
- Easy handling, smaller and lighter fixtures possible
- Boostable light levels
- Enables use at higher temperatures in any burning position. Longer lifetime, fewer early failures, consistent performance over time
- Reduces early lamp or lamp holder failures. Excellent current transfer
- Pure, white light; color point close to black body line

Features

- Philips FastFit
- Very short arc
- Compact design
- Flexible power range
- Philips pinch protection
- Innovative gold plated pins
- MSR filling

Application

- Entertainment

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Versions




MSR Gold™ 700, 700/2, 1200
FastFit



MSR Gold™ 1500, 2000, 2000/2,
2500/2 FastFit

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold™ 700 FastFit 1CT/4	15/16 in	3/16 in	2-9/16 in	2-5/8 in	2-9/16 in	4-7/16 in	2 in
MSR Gold™ 700/2 FastFit 1CT/8	15/16 in	3/16 in	2-9/16 in	2-5/8 in	2-9/16 in	4-7/16 in	2 in
MSR Gold™ 1200 FastFit 1CT/4	1-1/16 in	1/4 in	2-9/16 in	2-5/8 in	2-9/16 in	5-1/16 in	2 in

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold™ 2000/2 FastFit 1CT/8	1-3/8 in	5/16 in	2-5/8 in	2-11/16 in	2-11/16 in	5-5/16 in	2 in
MSR Gold™ 2500/2 FastFit 1CT/4	1-7/16 in	3/8 in	2-15/16 in	3 in	3 in	6-1/16 in	2 in
MSR Gold™ 1500 FastFit 1CT/4	1-1/8 in	1/4 in	2-9/16 in	2-5/8 in	2-9/16 in	5-1/16 in	2 in
MSR Gold™ 1500/1 FastFit 1CT/4	1-1/8 in	1/4 in	2-9/16 in	2-5/8 in	2-9/16 in	5-1/16 in	2 in
MSR Gold™ 2000 FastFit 1CT/8	1-3/8 in	5/16 in	2-5/8 in	2-11/16 in	2-11/16 in	5-5/16 in	2 in
MSR Gold™ 2000/1 FastFit 1CT/8	1-3/8 in	5/16 in	2-5/8 in	2-11/16 in	2-11/16 in	5-5/16 in	2 in

Controls and dimming

Dimmable	Yes
----------	-----

General information

Cap-Base	PGJX50
Life To 50% Failures (Nom)	750 h
Main Application	Entertainment
Operating Position	Universal

Operating and electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power (Nom)
286914	MSR Gold™ 700 FastFit 1CT/4	10.2 A	700 W
245621	MSR Gold™ 700/2 FastFit 1CT/8	10.2 A	700 W
286880	MSR Gold™ 1200 FastFit 1CT/4	15 A	1200 W
245605	MSR Gold™ 2000/2 FastFit 1CT/8	15.4 A	2000 W
287011	MSR Gold™ 2500/2 FastFit 1CT/4	19.53 A	2500 W

Order Code	Full Product Name	Lamp Current (Nom)	Power (Nom)
286971	MSR Gold™ 1500 FastFit 1CT/4	15.3 A	1500 W
260497	MSR Gold™ 1500/1 FastFit 1CT/4	15.3 A	1500.0 W
245738	MSR Gold™ 2000 FastFit 1CT/8	15.2 A	2000 W
323709	MSR Gold™ 2000/1 FastFit	18.2 A	2000 W

General information

Order Code	Full Product Name	System Description
286914	MSR Gold™ 700 FastFit 1CT/4	FastFit
245621	MSR Gold™ 700/2 FastFit 1CT/8	FastFit
286880	MSR Gold™ 1200 FastFit 1CT/4	FastFit
245605	MSR Gold™ 2000/2 FastFit 1CT/8	FastFit
287011	MSR Gold™ 2500/2 FastFit 1CT/4	FastFit


Order Code	Full Product Name	System Description
286971	MSR Gold™ 1500 FastFit 1CT/4	FastFit
260497	MSR Gold™ 1500/1 FastFit 1CT/4	FastFit
245738	MSR Gold™ 2000 FastFit 1CT/8	FastFit
323709	MSR Gold™ 2000/1 FastFit	-

Light technical

Order Code	Full Product Name	Color Code	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)	Luminous Flux (Min)	Luminous Flux (Nom)
286914	MSR Gold™ 700 FastFit 1CT/4	-	6000 K	79	-	54000 lm

Order Code	Full Product Name	Color Code	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)	Luminous Flux (Min)	Luminous Flux (Nom)
245621	MSR Gold™ 700/2 FastFit 1CT/8	2	7500 K	73	-	48000 lm
286880	MSR Gold™ 1200 FastFit 1CT/4	-	6000 K	80	-	100000 lm
245605	MSR Gold™ 2000/2 FastFit 1CT/8	2	7500 K	88	-	157000 lm
287011	MSR Gold™ 2500/2 FastFit 1CT/4	2	7200 K	88	-	195500 lm
286971	MSR Gold™ 1500 FastFit 1CT/4	-	6000 K	80	-	119550 lm
260497	MSR Gold™ 1500/1 FastFit 1CT/4	1	5700 K	85	-	127500 lm
245738	MSR Gold™ 2000 FastFit 1CT/8	-	6050 K	91	162000 lm	180000 lm
323709	MSR Gold™ 2000/1 FastFit	-	5700 K	90	155000 lm	172000 lm

Color Rendering Diagrams



XDCR_XDMSR_1200W-Colour Rendering
Vector diagram

