



MSR Hot Restrike – instant daylight at any time

MSR Hot Restrike

Thanks to an optimized color temperature and a high color rendering index, the MSR Hot Restrike creates perfect 'daylight' in any condition. Also, the single ended lamp design enables hot re-ignition, which ensures daylight lighting and superb color rendition is always instantly available. They also incorporate the innovative P3 technology, developed by Philips, which allows use at higher temperatures and therefore extends lifetime and consistency of high-quality light output.

Benefits

- Enables use at higher temperatures in any burning position. Longer lifetime, fewer early failures, consistent performance over time
- Perfect daylight color due to 6000K temperature with excellent color characteristics required for the set
- No arc movement
- High lumen output
- High beam intensity
- Hot re-ignition is possible ensuring the availability of the light at any time

Features

- Philips Pinch Protection
- MSR filling
- Optimal discharge tubes geometry
- High efficacy
- Single ended lamp concept
- Hot Restrike capability

MSR Hot Restrike

Application

- Indoor and outdoor filming
- Theaters
- Professional photography
- Solar simulation



Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



Dimensional drawing




Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 1200	40 mm	10.0	106	108 mm	107	200	67 mm	65	63 mm
HR 1CT/2		mm	mm		mm	mm		mm	

Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 575	30 mm	7.0	69 mm	71 mm	70	145 mm	43 mm	42	41 mm
HR 1CT/4		mm			mm			mm	

MSR Hot Restrike

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 400	23 mm	6.0	59 mm	61 mm	60	110 mm	24 mm	23.5	23 mm
HR 1CT/4		mm			mm			mm	

General Information	
Operating Position	UNIVERSAL
Light Technical	
Color Code	-
Controls and Dimming	
Dimmable	Yes

General Information

Order Code	Full Product Name	Cap-Base
22105000	MSR 575 HR 1CT/4	G22
22796000	MSR 400 HR 1CT/4	GZZ9.5

Order Code	Full Product Name	Cap-Base
92606400	MSR 1200 HR 1CT/2	G38

Light Technical

		Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux (Min)	Luminous Flux
Order Code	Full Product Name				
22105000	MSR 575 HR 1CT/4	6000 K	90	43,200 lm	48,000 lm
22796000	MSR 400 HR 1CT/4	5830 K	92	28,080 lm	31,200 lm

		Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux (Min)	Luminous Flux
Order Code	Full Product Name				
92606400	MSR 1200 HR 1CT/2	6000 K	95	-	103,000 lm

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
22105000	MSR 575 HR 1CT/4	6.75 A	575 W
22796000	MSR 400 HR 1CT/4	7 A	400 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
92606400	MSR 1200 HR 1CT/2	13.5 A	1,200 W

MSR Hot Restrike

