



MSR Gold™ MiniFastFit – lamp replacement in seconds

MSR Gold™ MiniFastFit (Touring/Stage)

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Avantages

- Lamp replacement in just seconds
- Easy handling, smaller and lighter fixtures
- Reduces early lamp or lamp holder failures. Excellent current transfer
- High perceived brightness
- High beam intensity

Fonctions

- Philips MiniFastFit
- Compact design
- Innovative gold plated pins
- High color temperature
- Very short arc

MSR Gold™ MiniFastFit (Touring/Stage)

Application

- Events
- Shows
- Touring/Stage

Mises en garde et sécurité

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Versions



Schéma dimensionnel



Product	D (max)	O	L (min)	L (max)	L	C (max)
MSR Gold™ 300/2	23 mm	5,0 mm	65,8 mm	67,8 mm	66,8 mm	126 mm
MiniFastFit 1CT/4						



Product
MSR Gold™ 700/2 MiniFastFit 1CT/4

MSR Gold™ MiniFastFit (Touring/Stage)

Commandes et gradation

Intensité réglable	Yes
--------------------	-----

Renseignements généraux

Culot	PGJX28
Durée de vie jusqu'à 50% des défaillances (nom.)	750 h
Application principale	Entertainment
Position de fonctionnement	Universal
Description du système	MiniFastFit

Données techniques sur l'éclairage

Code de couleur	2
-----------------	---

Fonctionnement et électricité

Order Code	Full Product Name	Courant de la lampe (nom.)	Puissance (nominale) (nom.)
287177	MSR Gold™ 300/2 MiniFastFit	3,75 A	300 W
	1CT/4		

Order Code	Full Product Name	Courant de la lampe (nom.)	Puissance (nominale) (nom.)
286922	MSR Gold™ 700/2 MiniFastFit	10,2 A	700 W
	1CT/4		

Données techniques sur l'éclairage

Order Code	Full Product Name	Température selon la couleur corrélée (nom.)	Indice de rendu des couleurs (nom.)	Flux lumineux (min.)	Flux lumineux (nom.)
287177	MSR Gold™ 300/2 MiniFastFit	9300 K	80	19170 lm	21300 lm
	1CT/4				

Order Code	Full Product Name	Température selon la couleur corrélée (nom.)	Indice de rendu des couleurs (nom.)	Flux lumineux (min.)	Flux lumineux (nom.)
286922	MSR Gold™ 700/2 MiniFastFit	7200 K	75	44000 lm	47000 lm
	1CT/4				

