



# Compact Source – for higher performance luminaires

## Compact Source

The very compact filament in the Compact Source series helps create a proportionately high beam intensity and the Compact Source range is therefore ideal for the latest generation of high-performance luminaires. Also, thanks to their low energy consumption, each dimmer can serve significantly more fixtures, thereby reducing overall dimmer costs. What's more, the Compact Source lamps incorporate the innovative P3 technology, developed by Philips, which enables the lamps to be used at higher temperatures in any burning position. This results in longer lamp lifetimes, reduced lamp replacement costs, and a more consistent lighting performance over the whole lifetime of the lamp.

### Benefits

- Enables use at higher temperatures in any burning position. Longer lifetime, fewer early failures, consistent performance over time.
- High beam intensity. Due to low energy consumption, more fixtures from each dimmer can be offered.

### Features

- Philips P3 pinch protection
- Very compact filament

### Application


- Studio, stage and entertainment lighting

Compact Source

Versions



Dimensional drawing



Product	D (max)	H	W	L	C (max)
6989P 575W G9.5 115V 1CT/10	19 mm	7.5 mm	9 mm	60.5 mm	101 mm

