



Halogen Low Voltage – long life, low costs

Halogen Low Voltage

The long lifetime of most of the Halogen Low Voltage lamps is further extended by the unique P3 technology developed by Philips. This allows the lamp to be used at higher temperatures, thereby extending the lamp's lifetime, reducing early failures, and resulting in fewer maintenance man hour costs. P3 also ensures consistency of high-quality light output, and allows the lamp to be used in any burning position, which enables more compact fixture designs. In addition, the compact filament produces a clean white light and high beam intensity for true natural colors on stage and without any hotspots.

Benefits

- Lower lamp replacement costs
- High beam intensity
- Pure colors on stage
- Allows creative use without hotspots or shadows

Features

- Lifetime up to 1000 hours due to Philips Pinch Protection
- Compact filament
- White light
- Even light distribution

Application

- These lamps are especially suitable for disco, moving beam, luminaires


Halogen Low Voltage

Versions



GZ6.35

Dimensional drawing



Product	D (max)	C (max)
6853 FO 75W GZ6.35 12V 1CT/10X5F	50 mm	42 mm

