



Halogen non-reflector lamps – high-quality light and easy to use

Halogen non-reflector

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.

优点

- Optimal beam performance
- 100% Color Rendering Index (CRI)
- Constant light output throughout lifetime

特点

- Distortion-free, quartz bulb and precisely defined filament position
- Lamp replacement without adjustment
- XHP version with xenon gas for maximum light output
- Flat filament available

Halogen non-reflector



应用

- Studio, film, theatre and disco lighting
- Slide, overhead, profile and 8/16 mm film projectors
- Microscopes
- Optical equipment
- Slide and film viewers
- Surgery lamps
- Microfilm readers
- Dental lamps
- Spectrography

Versions



二维绘图



Product			
7158XHP	150W	G6.35	24V 1CT/10X10F
6550	150W	G6.35	15V 1CT/10X10F
7023	100W	GY6.35	12V 1CT/10X10F
7724	100W	GY6.35	12V 1CT/10X10F
7027	50W	G6.35	12V 1CT/10X10F
7748XHP	250W	G6.35	24V 1CT/10X10F

Product	D (max)	L (max)	C (max)
5761 30W G4 6V 1CT/10X10F	9.5 mm	19.75 mm	31 mm
7388 20W G4 6V 1CT/10X10F	9.5 mm	19.75 mm	31 mm
7387 10W G4 6V 1CT/10X10F	9.5 mm	19.75 mm	31 mm
6605 10W G4 6V 1CT/10X10F	9.5 mm	19.75 mm	31 mm

Halogen non-reflector

基本信息	
主要应用	投影
照明科技	
显色指数 (标称)	100
机械和壳体	
灯泡材料	石英-不抗紫外线

运营和电气

Order Code	Full Product Name	电压 (标称) 功率 (额定)(标称)		Order Code	Full Product Name	电压 (标称) 功率 (额定)(标称)	
923870017103	7023 100W GY6.35 12V 1CT/10X10F	12 V	100 W	924031720503	7158XHP 150W G6.35 24V 1CT/10X10F	24 V	150 W
923872517103	7724 100W GY6.35 12V 1CT/10X10F	12 V	100 W	923873910103	6605 10W G4 6V 1CT/10X10F	6 V	10 W
923870217103	7027 50W G6.35 12V 1CT/10X10F	12 V	50 W	923874510103	7387 10W G4 6V 1CT/10X10F	6 V	10 W
923870618503	6550 150W G6.35 15V 1CT/10X10F	15 V	150 W	923874610103	7388 20W G4 6V 1CT/10X10F	6 V	20 W
924006520503	7748XHP 250W G6.35 24V 1CT/10X10F	24 V	250 W	923931110103	5761 30W G4 6V 1CT/10X10F	6 V	30 W

基本信息

Order Code	Full Product Name	Ansi 代码	底座	LIF 代码	50% 故障条件下的使用寿命 (标称)	操作位置	飞利浦代码
923870017103	7023 100W GY6.35 12V 1CT/10X10F	FCR	GY6.35	A1/215	50 h	S90	7023
923872517103	7724 100W GY6.35 12V 1CT/10X10F	EVA	GY6.35	M28	2000 h	S90	7724
923870217103	7027 50W G6.35 12V 1CT/10X10F	BRL-BCD	G6.35	A1/220	50 h	S90	7027
923870618503	6550 150W G6.35 15V 1CT/10X10F	EVB-BRJ	G6.35	A1/234	50 h	S90	6550
924006520503	7748XHP 250W G6.35 24V 1CT/10X10F	EHJ	G6.35	A1/223	50 h	S90	7748XHP
924031720503	7158XHP 150W G6.35 24V 1CT/10X10F	FCS	G6.35	A1/216	40 h	S90	7158XHP
923873910103	6605 10W G4 6V 1CT/10X10F	-	G4	M42	2000 h	UNIVERSAL	6605
923874510103	7387 10W G4 6V 1CT/10X10F	ESA	G4	M29	100 h	S90	7387
923874610103	7388 20W G4 6V 1CT/10X10F	ESB	G4	M30	100 h	UNIVERSAL	7388
923931110103	5761 30W G4 6V 1CT/10X10F	-	G4	-	100 h	UNIVERSAL	5761

照明科技

Order Code	Full Product Name	相关色温 (标称)	光通量 (标称)	光通量 (额定) (标称)	Order Code	Full Product Name	相关色温 (标称)	光通量 (标称)	光通量 (额定) (标称)
923870017103	7023 100W GY6.35 12V 1CT/10X10F	3450 K	-	3600 lm	924006520503	7748XHP 250W G6.35 24V 1CT/10X10F	3550 K	-	10000 lm
923872517103	7724 100W GY6.35 12V 1CT/10X10F	3300 K	-	2800 lm	924031720503	7158XHP 150W G6.35 24V 1CT/10X10F	3450 K	-	6000 lm
923870217103	7027 50W G6.35 12V 1CT/10X10F	3350 K	-	1600 lm	923873910103	6605 10W G4 6V 1CT/10X10F	2700 K	150 lm	-
923870618503	6550 150W G6.35 15V 1CT/10X10F	3450 K	-	5600 lm	923874510103	7387 10W G4 6V 1CT/10X10F	3200 K	200 lm	-
					923874610103	7388 20W G4 6V 1CT/10X10F	3350 K	460 lm	-
					923931110103	5761 30W G4 6V 1CT/10X10F	3200 K	765 lm	-

机械和壳体

Order Code	Full Product Name	灯丝外形	Order Code	Full Product Name	灯丝外形
923870017103	7023 100W GY6.35 12V 1CT/10X10F	平板	924006520503	7748XHP 250W G6.35 24V 1CT/10X10F	平板
923872517103	7724 100W GY6.35 12V 1CT/10X10F	平板	924031720503	7158XHP 150W G6.35 24V 1CT/10X10F	平板
923870217103	7027 50W G6.35 12V 1CT/10X10F	平板	923873910103	6605 10W G4 6V 1CT/10X10F	-
923870618503	6550 150W G6.35 15V 1CT/10X10F	平板	923874510103	7387 10W G4 6V 1CT/10X10F	-

Halogen non-reflector

Order Code	Full Product Name	灯丝外形
923874610103	7388 20W G4 6V 1CT/10X10F	-

Order Code	Full Product Name	灯丝外形
923931110103	5761 30W G4 6V 1CT/10X10F	-

