



Blue Pinch – high power, low weight

Blue Pinch

The small lamp size of the Blue Pinch series combined with the high performance pinch protection technology enables fixture manufacturers to create light and compact luminaires with a very high lumen output.

Benefits

- Meet the needs of fixture manufacturers who wish to create compact and lightweight luminaires without sacrificing lumen output or lamp life

Features

- Lamp pinch can be operated at up to 500°C
- Enables a significant reduction of light centre length (LCL), or an increase in lamp power by up to 300 per cent with same LCL, compared with unprotected lamps
- Biplane filament
- Unique pinch protection

Application


- Studio and film lighting
- Stage and theatre lighting
- Disco and show lighting

Blue Pinch

Versions



Dimensional drawing



Product	D (max)	H	W	L	C (max)
69951/BP 1000W GY9.5 240V 1CT/10	22 mm	14.5 mm	11 mm	46.5 mm	95 mm

