



# Blue Pinch – high power, low weight

## Blue Pinch

The small lamp size of the Blue Pinch series combined with the high performance pinch protection technology enables fixture manufacturers to create light and compact luminaires with a very high lumen output.

### Benefits

- Meet the needs of fixture manufacturers who wish to create compact and lightweight luminaires without sacrificing lumen output or lamp life

### Features

- Lamp pinch can be operated at up to 500°C
- Enables a significant reduction of light centre length (LCL), or an increase in lamp power by up to 300 per cent with same LCL, compared with unprotected lamps
- Biplane filament
- Unique pinch protection

### Application


- Studio and film lighting
- Stage and theatre lighting
- Disco and show lighting

# Blue Pinch

## Versions



## Dimensional drawing



Product	D (max)	H	W	L	C (max)
69951/BP 1000W GY9.5 240V 1CT/10	22 mm	14.5 mm	11 mm	46.5 mm	95 mm

