



Halogen High Voltage SE (Film/Studio) – stars on film and video

Halogen High Voltage SE (Film/Studio)

The high, constant output and consistent color temperature of these single ended halogen lamps ensure attractive, accurately exposed pictures for both film and video. Furthermore, these lamps incorporate the highly innovative P3 technology, developed by Philips. This allows the lamps to be used at higher temperatures, which extends overall lifetime and consistency of their high-quality light output. P3 technology also allows the lamp to be used in any burning position and enables more compact designs of fixtures. In addition, the very wide choice of dimensions and power ratings opens new levels of creative freedom for the luminaire designer.

优点

- Studio/film: High lumen output
- Studio/film: Enables use at higher temperatures in any burning position. Longer lifetime, fewer early failures, consistent performance over time.
- Video: Makes attractive, accurately exposed pictures possible

特点

- Studio/film: all lamps have a correlated color temperature of 3200K and P3 technology
- Video: high constant light output and color temperature

应用


- Studio/film: Studio, film, theater and disco lighting
- Video: Portable film and video lights, reproduction cameras

Halogen High Voltage SE (Film/Studio)

Versions



二维绘图



Product	D (max)	H	W	L	C (max)	P (max)	P (min)	R	K (max)	K (min)
6995P	23 mm	14.5	11	55	110	3.25	3.10	9.53	9.2 mm	8.4
1000W		mm	mm	mm	mm	mm	mm	mm		mm
GX9.5										
230V										
1CT/10										

