



PAR56 and PAR 64 – picking out the smallest of details

PAR56 and PAR64

These self-contained spotlights are ideal for intensifying the visual experience in all kinds of clubs, that is because their accurate beam control picks out even the smallest of details even over long distances. This beam control makes the PAR 56 and PAR 64 excellent for long-range light projections. In addition, the universal burning feature provides complete flexibility of luminaires angle and position, while the front glass of the PAR56 provides thermal and physical protection. The result? Complete creative freedom to achieve the desired effect. Immediate re-strike also ensures instant resumption of entertainment after any power interruption.

Benefits

- $\boldsymbol{\cdot}$ Allows details to be picked out over long distances with good beam control
- Excellent for long-range light projections
- · Provides thermal and physical protection
- Allows fullest flexibility of luminaire angle and position to obtain the desired effect
- · Immediate re-strike after any power interruption

Features

- · Self-contained spotlight
- Front glass
- Universal burning
- · Hot restrike

Application

• Ideal for a wide range of performance and event lighting applications, for example in clubs, studios and theaters

PAR56 and PAR64


Versions





PAR64 PAR56

Dimensional drawing



Product	D (max)	C (max)
Par56 MFL 300W 240V GX16d.1CT/6	178 mm	127 mm
PAR64 1000W 240V MFL	204 mm	150 mm
PAR64 1000W 240V NSP	204 mm	150 mm

Yes
240 V
GX16D
Flood and
Ambient Lighting
UNIVERSAL

Operating and Electrical

Order Code	Full Product Name	Power (Rated) (Nom)
924783345504	PAR64 1000W 240V NSP	1000 W
924783445504	PAR64 1000W 240V MFL	1000 W

Order Code	Full Product Name	Power (Rated) (Nom)
924783645504	Par56 MFL 300W 240V GX16d.1CT/6	300 W

General Information

PAR56 and PAR64

				Nominal	
		Ansi	LIF	Lifetime	Life To 50%
Order Code	Full Product Name	Code	Code	(Nom)	Failures (Min)
924783345504	PAR64 1000W	EXD	CP61	300 h	300 h
	240V NSP				
924783445504	PAR64 1000W	EXE	CP62	300 h	300 h
	240V MFL				

				Nominal	
		Ansi	LIF	Lifetime	Life To 50%
Order Code	Full Product Name	Code	Code	(Nom)	Failures (Min)
924783645504	Par56 MFL 300W	-	-	2000 h	2000 h
	240V GX16d.1CT/6				
	•				

Light Technical

				Correlated	
		Beam		Color	Luminous
	Full Product	Angle	Beam	Temperature	Intensity
Order Code	Name	(Nom)	Description	(Nom)	(Max)
924783345504	PAR64	12 °	Narrow Spot	3200 K	290000 cd
	1000W 240V				
	NSP				
924783445504	PAR64	23°	Medium	3200 K	130000 cd
	1000W 240V		Flood		
	MFL				

				Correlated	
		Beam		Color	Luminous
	Full Product	Angle	Beam	Temperature	Intensity
Order Code	Name	(Nom)	Description	(Nom)	(Max)
924783645504	Par56 MFL	20 °	Medium	3000 K	30000 cd
	300W 240V		Flood		
	GX16d.1CT/6				

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
924783345504	PAR64 1000W 240V NSP	PAR64
924783445504	PAR64 1000W 240V MFL	PAR64

Order Code	Full Product Name	Bulb Shape
924783645504	Par56 MFL 300W 240V GX16d.1CT/6	-

Approval and Application

Order Code	Full Product Name	Energy Efficiency Label (EEL)
924783345504	PAR64 1000W 240V NSP	-
924783445504	PAR64 1000W 240V MFL	-

Order Code	Full Product Name	Energy Efficiency Label (EEL)
924783645504	Par56 MFL 300W 240V GX16d.1CT/6	Not applicable



© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.