



Product Description

Flexo Print

Tubular low-pressure mercury vapour discharge lamps

Benefits

- Best match with photo sensitizers
- Highest output on irradiated area

Features

- Internally coated with a white fluorescent powder to convert the short-wave UV radiation into useful actinic radiation
- Emit radiation in the range 380 - 480 nm with a maximum at 420 nm
- Spectral energy distribution in accordance with the spectral sensitivity of a number of diazo copying papers
- For maximum beauty of marine aquaria, TL /03 "Aqua Coral" lamps can be used in combination with full-spectrum "Natural Daylight" fluorescent lamps

Application


- Diazo copying machines
- Marine aquaria
- Phototherapy (neonatal jaundice treatment)

Flexo Print

Versions



Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 140W/03	40.5 mm	1500 mm	1507.1 mm	1504.7 mm	1514.2 mm

