



# Energy-efficient lighting for industrial and commercial applications

## GreenPerform Hygeia

Customers operating highly hygienic facilities require, easy-to-clean, dust-free luminaires that meet all lighting requirements and norms. The New Hygeia with a IP40 and compliance to 1,000 – 100,000 class cleanroom makes It a good choice. The new Hygeia CR308 has a streamlined shape that minimizes dust gathering and disturbed airflow. The cleanroom luminaire uses the latest Philips LED Line platform to provide most value for money. This means extremely low operational cost over the total lifetime of the luminaire, and so an excellent financial return on investment.

### Benefits

- Professional design, treamlined shape minimizes dust gathering and disturbed airflow
- Reliable and sustainable lifetime
- Slim and lithier, 7kgs, easy to install

### Features

- Suitable for 1,000 to 100,000 Class cleanroom
- IP40 with smooth surface and easy to clean
- 30% lighter compare to the older version

### Application

- Semiconductor and electronics industry
- Pharmaceutical industry
- Healthcare
- Food and beverage industry
- Precision instruments
- Fine mechanics
- Research and laboratories

