



Philips TubeLine: linear tunnel lighting for optimized comfort and guidance

TubeLine

For customers who demand a high level of visual comfort from their tunnel luminaires, fluorescent linear lighting has traditionally been the preferred choice. With excellent light uniformity on the road and walls, perfect visual guidance and high color rendering, linear lighting offers drivers superior lighting quality and safety. It also promises high system redundancy compared to point source lighting solutions. With Philips TubeLine tunnel luminaires, you can achieve the same lighting quality, but with all the added advantages of LED technology. TubeLine is a state-of-the-art tunnel luminaire that harnesses the latest LED technology with optimized dimensions and attractive pricing for a quick return on investment. Linear lighting has never been more achievable for tunnel lighting and underpass lighting on a limited budget.

Benefits

- Optimal traffic flow due to increased visual comfort and safety compared to point-source lighting
- Economical alternative to fluorescent tunnel lighting
- High tunnel lighting availability: remote driver system
- Flexible, easy-to-install lighting system


Features

- Linear luminaire in 1 or 2 meter lengths
- Driver not integrated: remote driver set-up
- Wide range of lumen packages: 3,000 to 30,000 lm
- Multiple mounting and connectivity options
- Compatible with tunnel controls from Philips and third parties
- Service tag: QR-based identification for maintenance, installation and spare part information

Application

- Tunnel
- Underpass

Dimensional drawing



Product details

TubeLine_BGP360-DP01.tif



TubeLine_BGP360-DP02.tif



TubeLine_BGP360-DP03.tif



TubeLine_BGP360-DP04.tif



Product details


TubeLine_BGP360-DP05.tif



TubeLine_BGP360-DP06.tif



TubeLine_BGP360-DP07.tif



TubeLine_BGP360-DP08.tif



TubeLine_BGP360_ZGP360-DP09.tif



General Information	
CE mark	Yes
Driver included	No
Flammability mark	-
Gear	-
Light source replaceable	No
Number of gear units	1 unit
Product family code	BGP360
Light Technical	
Luminaire light beam spread	150°
Light source color	740 neutral white
Correlated Color Temperature (Nom)	4000 K
Optical cover type	Flat glass
Color rendering index (CRI)	≥80
Optic type outdoor	Distribution tunnel symmetrical
Standard tilt angle side entry	-
Standard tilt angle posttop	-
Upward light output ratio	0
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	Aluminum
Approval and Application	
Mech. impact protection code	IK08
Ingress protection code	IP66
Surge Protection (Common/ Differential)	-

General Information

Order Code	Full Product Name	Lamp family code
912300023650	BGP360 LED30/740 DTS CFW C250W GP	LED30
912300023651	BGP360 LED60/740 DTS CFW C250W GP	LED60
912300023653	BGP360 LED120/740 DTS CFW C250W GP	LED120
912300023654	BGP360 LED165/740 DTS CFW C250W GP	LED165

Light Technical

Order Code	Full Product Name	Luminous Flux	Number of light sources
912300023650	BGP360 LED30/740 DTS CFW C250W GP	2,700 lm	24
912300023651	BGP360 LED60/740 DTS CFW C250W GP	5,400 lm	48

Order Code	Full Product Name	Luminous Flux	Number of light sources
912300023653	BGP360 LED120/740 DTS CFW C250W GP	10,800 lm	48
912300023654	BGP360 LED165/740 DTS CFW C250W GP	14,685 lm	48

Operating and Electrical

Order Code	Full Product Name	Power Consumption
912300023650	BGP360 LED30/740 DTS CFW C250W GP	18.8 W
912300023651	BGP360 LED60/740 DTS CFW C250W GP	35.5 W

Order Code	Full Product Name	Power Consumption
912300023653	BGP360 LED120/740 DTS CFW C250W GP	72 W
912300023654	BGP360 LED165/740 DTS CFW C250W GP	104 W

