



FlowLine LED unit – linear LED tunnel luminaire

FlowLine

Tunnels often require a linear interior lighting solution. FlowLine offers an LED solution where traditionally fluorescent lighting was used. FlowLine outperforms fluorescent lighting over the full life cycle in terms of cost, safety and performance, and is a competitive alternative to HPS point-source interior lighting on total cost of ownership. Its linear build allows continuous or spaced line lighting schemes, providing optimal guidance and a high level of visual comfort. Performance can be further optimized by using FlowLine in combination with our dedicated lighting controls and service packages.

Benefits

- Linear LED lighting ensuring safety and visual comfort
- Highly efficient lifetime solution
- Designed as part of the TotalTunnel approach for easy installation as well as reduced maintenance and lifecycle cost

Features

- Stainless-steel modular build
- Dedicated LED design
- Long-lasting
- Designed for maintenance (modular build and glass cover)
- Can be integrated with controls and service packages for best system performance

Application

- Traffic tunnels
- Underpasses

Versions



Product details



Product details

