



# LuxSpace surface-mounted – high efficiency, visual comfort and a stylish design

## LuxSpace Mini, surface mounted

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (color rendering and color uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application.

### Benefits

- Best-in-class efficacy
- Creates a gentle, natural light, ensuring visual comfort

## LuxSpace Mini, surface mounted

### Features

- Choice of four optics: high-gloss, faceted, matt and white
- Heights: deep (up to UGR 19), low (up to UGR 22)
- Colors: high-gloss metalized, white (RAL9010), grey, black (RAL9004) as standard (any other RAL color possible upon request)
- Recessed version available
- Compliant for central emergency lighting with DC
- 3C track version (upon request)
- Multiple additional options: PG and PGO, suspended deco glass

### Application

- Offices
- Retail
- Hospitals
- Hotels
- Airports

### Specifications

<b>Type</b>	DN560C (low height surface-mounted version)
	DN561C (deep surface-mounted version)
<b>Light source</b>	Non replaceable LED module
<b>Power</b>	8 or 11.2 W (depending on configuration)
<b>Luminous flux</b>	780 to 1200 lm (depending on configuration)
<b>Correlated Color</b>	2700, 3000 or 4000 K
<b>Temperature</b>	
<b>Color Rendering Index</b>	> 80
	90 (available in 3000 K)
<b>Median useful life</b>	70,000 hours
<b>L70B50</b>	
<b>Median useful life</b>	50,000 hours
<b>L80B50</b>	
<b>Median useful life</b>	25,000 hours
<b>L90B50</b>	
<b>Average ambient temperature</b>	25 °C
<b>Operating temperature range</b>	+10 to +40 °C

<b>Driver</b>	Separate
<b>Mains voltage</b>	230 or 240 V / 50-60 Hz
<b>Dimming</b>	DALI dimming possible (PSED-E)
<b>Options</b>	Protection glass (PG or PGO)
	Suspended glasses: opal (SG-O), frosted circle (SG-FRC) and frosted halo ring (SG-HR-FR)
	3C track version (upon request)
<b>Material</b>	Housing and rim: aluminum
	Reflector: plastic, aluminum coated (for high-gloss and faceted optics)
<b>Color</b>	Rim: white (RAL 9010), grey (similar to RAL 9006), black (RAL 9005) or high-gloss metalized
<b>Optic</b>	High-gloss mirror (C)
	Matt mirror (M)
	Faceted reflector (F)
	White reflector (WR)
<b>Connection</b>	Push-in connector or with pull relief
<b>Installation</b>	Individual, screw mounting
<b>Remarks</b>	External driver included

### Accessories

Protection glass

Ordercode 910503706523



Protection glass, opal

Ordercode 910503706524



## LuxSpace Mini, surface mounted

