



# The affordable LEDspot solution

## CorePro LEDspot MV

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 or E14 holder and are designed as a retrofit replacement for halogen or incandescent spots. LEDlamps deliver huge energy savings and minimize maintenance cost.

### Benefits

- Warm white light
- Warm white light
- Up to 80% energy saving compared with halogen lamps
- Up to 80% energy saving compared with halogen lamps
- Lower maintenance costs
- Lower maintenance costs
- Broad compatibility with transformers
- Broad compatibility with transformers

### Features

- Easy retrofit
- Easy retrofit
- Lifetime of 15,000 hours
- Lifetime of 15,000 hours
- Compatible with an extensive range of dimmers
- Compatible with an extensive range of dimmers
- UV- and IR-free light
- UV- and IR-free light
- Free of mercury and hazardous materials
- Free of mercury and hazardous materials

# CorePro LEDspot MV

## Application


- Hotels, restaurants, bars, cafés, museums, shops
- Hotels, restaurants, bars, cafés, museums, shops
- Lobbies, corridors, stairwells, washrooms, reception areas , exhibitions, display cabinets
- Lobbies, corridors, stairwells, washrooms, reception areas , exhibitions, display cabinets

## Versions




CorePro LEDspot MV 25W GU10 830 36D


## Dimensional drawing



Product	D	C
Essential LED 4.6-50W GU10 865 36D	50 mm	54 mm




Accent Diagrams



Accent Diagram - Essential LED 4.6-50W GU10  
865 36D

Beam Diagrams



Beam diagram - Essential LED 4.6-50W GU10  
865 36D

