



Mini 300 Cube – daylight impression

Mini 300 Cube DGP300

Mini 300 Cube is an extremely efficient low-glare luminaire specially designed for downlighting. The efficiency is achieved by a special optic coating, which reflects 97% of the light, and by the use of CDM-TD 4200 K lamps. The combination of this lamp and the white-coated reflector creates an inviting atmosphere with color rendering of 96. Mini 300 Cube delivers a uniform light distribution with an asymmetric or bi-directional beam creating outstanding illuminances in industrial and retail environments. The range comprises versions for recessed (DBP300), surface mounted (DCP300) and post/wall mounted (DGP300). Within the Mini 300 product family there is also a dedicated floodlight version (Mini 300 Stealth). Mini 300 is also available in LED versions (Mini 300 LED) in high efficiency for substantial energy savings.

Faydaları

- Creates a daylight impression with an extremely efficient low-glare luminaire specially designed for downlighting in canopies
- Uniform light distribution with asymmetrical or bi-directional beam for outstanding illuminance in industrial and retail environments
- Inviting atmosphere thanks to CDM-TD lamp with excellent color rendering and white-coated reflector

Özellikler

- CDM-TD ampul
- Beyaz kaplamalı reflektör
- Asimetrik veya çift yönlü ışın
- CRI 96
- Gömülü, yüzeye ve ardıl/duvara montaj için modeller

Mini 300 Cube DGP300

Uygulama

- Servis istasyonları
- Kamusal alanlar
- Araç park yerleri
- Güvenlik aydınlatması
- Alışveriş merkezleri

ÜRÜN BİLGİLERİ

