



Standard electromagnetic ballast for compact fluorescent applications

BPL EM ballasts for CFL, PL-T, PL-S and PL-C lamps

This standard, reliable, long-life electromagnetic ballast for compact fluorescent lamps provides excellent performance with 2-pin and 4-pin CFLni lamps.

Benefits

- Reliable electrical and mechanical performance
- Optimum lamp performance under optimum temperature conditions
- Fits compact luminaires

Features

- Long lifetime
- Compact design
- Quick and easy wiring
- High-quality screw-in or insert contact

Application

- Retail
- Offices
- Industry
- Home

BPL EM ballasts for CFL, PL-T, PL-S and PL-C lamps

Versions



BPL 26W 220V B2 SC

Dimensional drawing

A1

Product	D1	C1	A1	A2	A3	A4	B1
BPL 18W 220V/ 60Hz B2 SC	4.3 mm	28.0 mm	85.0 mm	75.0 mm	31.0 mm	30.0 mm	39.0 mm

