



DALI Square Track – flexibility enabling energy savings

DALI Square Track

Designed for use with DALI projectors with a dedicated adaptor, the DALI Square Track is ideal for users who want lighting flexibility to create a specific ambience in their shop and to reduce energy consumption. The system is made up of a solid aluminium track, which is available in various lengths and with a choice of electrical conductors. Any given configuration can be easily created – horizontal or vertical, mounted on or in the ceiling, on the wall or on free-standing panels. The system can also be used as a floating structure. All luminaires have a separate power supply and can be switched selectively. They can easily be moved to alter the lighting and presentation. In this way, a multifunctional track system can be created for accent lighting as well as for suspending advertising and decorative material.

Benefits

- Allows flexible light settings
- Enables energy savings
- Unobtrusive smart track

Features

- Integration of the DALI protocol within an unobtrusive retail spot track widely used for dimming and control
- Can be used with all Philips LED 3C track spots
- Available in lengths of 1, 2, 3 and 4 m
- Seven electrical conductors: L1/L2/L3/neutral/ground 16A/400V, IP20 + DA/DA 2x1A/50V FELV AC (DALI)
- Available in three finishes – white, black, aluminium
- Range of adaptors, power supply connections and mounting accessories available

DALI Square Track

Application


- Accent lighting in retail outlets, shopping malls, museums
- All indoor architectural lighting applications

Versions



ZCS750 5C6 IPC BK (XTSC621-2)


Dimensional drawing



DALI Square Track

Product details

IPDP_RCS750i_0001-Detail photo



General Information

Accessory color	Black
-----------------	-------

General Information

Order Code	Full Product Name	Glow-wire test	Glow-wire test
910502500078	ZCS750 5C6 CCPI BK (XTSC634-2)	-	-
910502500081	ZCS750 5C6 CCPE BK (XTSC635-2)	-	-
910502500075	ZCS750 5C6 IPC BK (XTSC621-2)	-	-

Order Code	Full Product Name	Glow-wire test	Glow-wire test
910502500045	RCS750 5C6 L3000 BK (XTSC6300-2)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
910502500048	RCS750 5C6 L2000 BK (XTSC6200-2)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s

Approval and Application

Order Code	Full Product Name	Protection class IEC	Protection class IEC	Ingress protection code	Ingress protection code
910502500078	ZCS750 5C6 CCPI BK (XTSC634-2)	-	-	-	-
910502500081	ZCS750 5C6 CCPE BK (XTSC635-2)	-	-	-	-
910502500075	ZCS750 5C6 IPC BK (XTSC621-2)	-	-	-	-

Order Code	Full Product Name	Protection class IEC	Protection class IEC	Ingress protection code	Ingress protection code
910502500045	RCS750 5C6 L3000 BK (XTSC6300-2)	Safety class I	Safety class I	IP30	IP30
910502500048	RCS750 5C6 L2000 BK (XTSC6200-2)	Safety class I	Safety class I	IP30	IP30

