



For reliable unveiling of secrets

TL Blacklight Blue

TL/08 Blacklight Blue lamps are low-pressure mercury-vapor fluorescent lamps. They have an inner envelope coated with a fluorescent powder that emits long-wave UV radiation to excite luminescence.

Benefits

- Quick detection of UV-reflecting materials
- Creates special lighting atmospheres and effects

Features


- Straight outer envelope

Application

- Detection and analysis in the textile and chemical industries
- Banking and forensic science
- Special effects in night clubs, discos and theaters, and sign lighting


TL Blacklight Blue

Versions



TL Blacklight Blue T38 G13

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
F40T12/BLACKLIGHT/48	40.5 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm
BLB LF					

