



Compact and robust

ConTempo 152-252-352

The ConTempo projector has a highly innovative design. It is made of cast aluminum with a powder coating, which makes it more robust for use outdoors. It has a dedicated housing for auxiliary equipment (ballast, igniter and capacitor), mounted on an aluminum chassis, which ensures excellent heat dissipation.

Benefits

- Lightweight, compact
- Philips solution: lamp, ballast, and luminaire
- IP65: provides increased security for the installation and protects equipment within the luminaire
- Anodized aluminum reflector ensures excellent light distribution
- Tempered glass front
- Stainless-steel fixing clips
- Two beam options: greater flexibility for the designer

Features

- Seamless integration with the architecture of the site
- Extremely robust and resistant for outdoor use
- Equipped with ballast, capacitor, and igniter
- Available in symmetrical and asymmetrical versions
- Easy maintenance and access to parts

Application


- Functional: ports, storage areas, parking areas, construction sites
- Recreation / sports: training grounds, sports courts, swimming pools
- Decorative: facades, buildings, billboards, gardens, courtyards, fountains, bridges, landscapes

Specifications

ConTempo 152-252-352

Type	RVP152
	RVP252
	RVP352
Power supply	220 V
Frequency	60 Hz
Number of lamps	1
Power and lamp models	1 x CDM-T / G12 / 35 W
	1 x CDM-TD / RX7S / 70 W
	1 x CDO-TT / E27 / 70 W
	1 x MHN-TD / RX7S / 70, 150 W
	1 x SON-T / E27 / 70 W
	1 x SON-T / E40 / 150, 250, 400 W
	1 x CDM-TD / RX7S-24 / 150 W
	1 x HPI-T / E40 / 250, 400 W

Versions



General Information

Order Code	Full Product Name	Light source color	Lamp family code	Lamp power	Optic type
919306012859	RVP352 SON-T250W K 220V-60Hz A	-	SON-T	250 W	Asymmetrical
919306012867	RVP352 SON-T250W K 220V-60Hz S	-	SON-T	250 W	Symmetrical
919306012877	RVP352 SON-T400W K 220V-60Hz A	-	SON-T	400 W	Asymmetrical
919306012889	RVP352 SON-T400W K 220V-60Hz S	-	SON-T	400 W	Symmetrical
919306012891	RVP352 HPI-TP250W K 220V-60Hz A	-	HPI-TP	250 W	Asymmetrical
919306012901	RVP352 HPI-TP250W K 220V-60Hz S	-	HPI-TP	250 W	Symmetrical
919306012917	RVP352 HPI-TP400W K 220V-60Hz A	-	HPI-TP	400 W	Asymmetrical
919306012927	RVP352 HPI-TP400W K 220V-60Hz S	-	HPI-TP	400 W	Symmetrical

Order Code	Full Product Name	Light source color	Lamp family code	Lamp power	Optic type
919306012969	RVP252 SON-T150W K 220V-60Hz A	-	SON-T	150 W	Asymmetrical
919306012979	RVP252 SON-T150W K 220V-60Hz S	-	SON-T	150 W	Symmetrical
919306012989	RVP252 MHN- TD150W/842 220V-60Hz A	842 neutral white	MHN-TD	150 W	Asymmetrical
919306012995	RVP252 MHN- TD150W/842 220V-60Hz S	842 neutral white	MHN-TD	150 W	Symmetrical
919306012999	RVP252 CDM- TD150W/830 220V-60Hz A	830 warm white	CDM-TD	150 W	Asymmetrical
919306013129	RVP152 SON-T70W K 220V-60Hz S	-	SON-T	70 W	Symmetrical
919306013139	RVP152 SON-T70W K 220V-60Hz A	-	SON-T	70 W	Asymmetrical

ConTempo 152-252-352

Order Code	Full Product Name	Light source color	Lamp family code	Lamp power	Optic type
919306013149	RVP152 MHN-TD70W/842 220V-60Hz S	-	MHN-TD	70 W	Symmetrical
919306013159	RVP152 MHN-TD70W/842 220V-60Hz A	842 neutral white	MHN-TD	70 W	Asymmetrical
919306013161	RVP152 CDM-T35W/830 220V-60Hz S	830 warm white	CDM-T	35 W	Symmetrical
919306013171	RVP152 CDM-T35W/830 220V-60Hz A	830 warm white	CDM-T	35 W	Asymmetrical
919306013189	RVP152 CDM-TD70W/830 220V-60Hz S	830 warm white	CDM-TD	70 W	Symmetrical

Order Code	Full Product Name	Light source color	Lamp family code	Lamp power	Optic type
919306013191	RVP152 CDM-TD70W/830 220V-60Hz A	830 warm white	CDM-TD	70 W	Asymmetrical
919306013195	RVP152 A CDM-TD70W/942 220V-60Hz A	942 neutral white	CDM-TD	70 W	Asymmetrical
919306013271	RVP152 CDO-TT70W K 220V-60Hz A	-	CDO-TT	70 W	Asymmetrical
919306013281	RVP152 CDO-TT70W K 220V-60Hz S	-	CDO-TT	70 W	Symmetrical

