



# Design and performance that blends with the architecture

## Selenium SGP340 A

The Selenium range offers efficiency combined with design. Its simple rounded forms reduce its visual impact, allowing for a more seamless integration into any environment. Selenium incorporates the renowned T-POT reflector which ensures excellent optic performance. Additional energy saving is made possible by the use of controls (e.g. Chronosense).

### Benefits

- Lightweight, compact
- Philips solution: lamp, ballast, and luminaire
- IP66: provides increased security for the installation and protects equipment within the luminaire
- High-purity aluminum reflector ensures excellent light distribution
- Tempered glass front
- Stainless-steel fixing clips
- Device allowing the luminaire to be tilted between 0.5 and 15°

### Features

- Product designed to have as little impact as possible on the existing architecture
- Very robust luminaire with IP66 for both the optics compartment and the ballast housing
- Easy maintenance - no tools required for interior access
- Reflector designed with the latest technology to make maximum use of light
- Flexibility of installation through the luminaire's angling device

# Selenium SGP340 A

## Application

- Residential streets
- Avenues
- Roads
- Industrial yards
- Parking lots
- Traffic circles

## Specifications

Type	SGP340
Power supply	220 V
Frequency	60 Hz

Power and lamp models	1 x SON-T / E40 / 150, 250, 400 W
	1 x CDO-TT / E40 / 100, 150 W
	1 x MASTER CosmoWhite CPO-TW / PGZ12 / 60, 140 W

## Versions



### General Information

Optical cover/lens type	Flat glass
-------------------------	------------

## General Information

Order Code	Full Product Name	Lamp family code	Lamp power
919306013231	SGP340 HPI-TP250W K 220V-60Hz I FG 48/60	HPI-TP	250 W
919306013301	SGP340 SON-TP150W K 220V-60Hz I FG 48/60	SON-TP	150 W
919306013311	SGP340 SON-TP250W K 220V-60Hz I FG 48/60	SON-TP	250 W
919306013321	SGP340 CDO-TT100W K 220V-60Hz I FG 48/60	CDO-TT	100 W

Order Code	Full Product Name	Lamp family code	Lamp power
919306013331	SGP340 CDO-TT150W K 220V-60Hz I FG 48/60	CDO-TT	150 W
919306014601	SGP340 A SON-TP400W 220V-60Hz I FG 48/60	SON-TP	400 W
919306014611	SGP340 A HPI-TP400W 220V-60Hz I FG 48/60	HPI-TP	400 W

