



# Appropriate choice for many fluorescent lamp types on the market

## Standard

Available for many fluorescent lamp types sold today, including Preheat, Rapid Start, 2-pin CFL, Slimline, High Output, Very High Output and Circline. Magnetic ballasts can be used in any application where these lamps are used.

### Benefits

- 60 HZ lamp operation eliminates possible EMI/RFI interference

### Features

- Only choice for many low volume lamp types on the market

### Application


- General office, warehouses, gymnasiums, manufacturing facilities, parking garages

## Versions



Standard

Dimensional drawing



Product	A1	A2	B1	C1
STANDARD RS3240TPWI	6.5 in	6 in	2.38 in	1.5 in

