



Vaya Linear MP – reliable, cost-effective LED linear fixture

Vaya Linear MP

Vaya Linear MP is a reliable and cost-effective LED lighting fixture designed for fixed or dynamic colorful lighting effects. Offering a choice of wide or elliptical beams, Vaya Linear MP is ideal for wall washing and grazing applications. Integrated power and unified power and data connectors make installation fast, easy and reliable.

Benefits

- Economical solution
- Suitable for harsh outdoor environments requiring relatively high light output
- Fast and easy installation

Features

- IP66-rated housing and connectors
- Relatively high light output
- Available with 10 x 50 or 50° beams
- Auto-ranging 100-277 V, 50/60 Hz input
- DMX512 control (RGB version)
- Dedicated connectors for quick, easy and secure installation

Application

- Grazing lighting of monuments, bridges, shops, hotels

Specifications

Type	BCP424 (RGB version)
	BCP425 (white light version)
	BCP426 (mono-color light version)

Light source	Built-in LED-module
Power	18 W / 60 W
Beam angle	10 x 50 and 50°

Vaya Linear MP

Luminous flux	450-1800 lm (RGB)
	840-3400 lm (white light)
Luminaire efficacy	50 lm/W
Correlated Color	3000 or 4000 K (2700 K and 5000 K custom options)
Temperature	RGB
Color Rendering Index	78
Maintenance of lumen output - L70	60,000 hours at 25°C
Operating temperature range	-40 to +40 °C
Driver	Integrated

Mains voltage	100-277 VAC / 50-60 Hz
Controls system input	DMX control for RGB versions
Optic	Asymmetrical or wide beam
Optical cover	Glass, transparent
Material	Housing: extruded aluminum
	Cover: glass, tempered
Color	Gray, RAL7043
Connection	Daisy-chain power input and output connectors
Installation	Surface mounting
	Location adjustable and tilting surface-mounting bracket
Remarks	Leader cables and jumper cables should be ordered separately

Versions

Vaya Linear MP BCP424/425/426
floodlight, 0.3 m



Vaya Linear MP BCP424/425/426
floodlight, 1.2 m



Accessories

Leader cable for white version, 15 m

Ordercode 62671899



Jumper cable for white version, 1,5 m

Ordercode 62672599



Leader cable for RGB version, 15 m

Ordercode 62673299



Jumper cable for RGB version, 1,5 m

Ordercode 62674999



