



Graze MX Powercore – high-intensity illumination of multi- storey façades and surfaces

eW Graze MX Powercore

Many architectural structures need a linear fixture capable of illuminating multiple storeys with minimal setback. Property owners/end users need a controllable product capable of dynamic illumination to draw attention to their establishments and emphasise their brands. Graze MX Powercore is capable of illuminating over 20 meters at very close setback distances. Powercore technology enables simple installation and long product run lengths.

Benefits

- Superior light quality, consistency and output thanks to Philips Color Kinetics Optibin and Chromasync technologies
- Simple installation and long run lengths enabled by Powercore technology
- Static and dynamic lighting effects can be designed, displayed and changed via Philips Color Kinetics controllers

Features

- Highest-intensity exterior-rated linear LED luminaire in the market
- High output and beam quality thanks to holographic diffusion technology
- Unparalleled control via adjustable dimming curves and transition speeds
- Superior output matching from fixture to fixture thanks to Optibin and Chromasync technologies

Application

- Illumination of exterior facades and structures
- Illumination of large architectural details
- Flood- and wash-lighting applications (depending on beam angle)

Versions

	eW Graze Powercore BCS419, svítidlo pro architektonické osvětlení, 305 mm		eW Graze Powercore BCS419, svítidlo pro architektonické osvětlení, 24 LED, 609 mm
	eW Graze Powercore BCS419, svítidlo pro architektonické osvětlení, 914 mm		eW Graze Powercore BCS419, svítidlo pro architektonické osvětlení, 36 LED, 1219 mm

Product details

	OPDP_BCS419i_0001-Detail photo	
--	-----------------------------------	--

Product details

OPDP_BCS419i_0005-Detail
photo



OPDP_BCS419i_0007-Detail
photo



OPDP_BCS419i_0011-Detail photo

