



ColorGraz MX Powercore – high- intensity illumination of multi-storey façades and surfaces

ColorGraz MX Powercore

Many architectural structures need a linear fixture capable of illuminating multiple storeys with minimal setback. Property owners/end users need a controllable product capable of dynamic illumination to draw attention to their establishments and emphasise their brands. Graze MX Powercore is capable of illuminating over 20 metres at very close setback distances. Powercore technology enables simple installation and long product run lengths.

Benefits

- Superior light quality, consistency and output thanks to Philips Color Kinetics Optibin and Chromasync technologies
- Simple installation and long run lengths enabled by Powercore technology
- Static and dynamic lighting effects can be designed, displayed and changed via Philips Color Kinetics controllers

Features





- Highest-intensity exterior-rated linear LED luminaire in the market
- High output and beam quality thanks to holographic diffusion technology
- Unparalleled control via adjustable dimming curves and transition speeds
- Superior output matching from fixture to fixture thanks to Optibin and Chromasync technologies

ColorGrazе MX Powercore

Application

- Illumination of exterior facades and structures
- Illumination of large architectural details
- Flood- and wash-lighting applications (depending on beam angle)

Versions

	<p>Svítidlo pro architektonické osvětlení ColorGrazе MX Powercore BCS459 (RGB, 1219 mm)</p>		<p>Svítidlo pro architektonické osvětlení ColorGrazе MX Powercore BCS459 (RGB, 305 mm)</p>
	<p>Svítidlo pro architektonické osvětlení ColorGrazе MX Powercore BCS459 (RGB, 609 mm)</p>		<p>Svítidlo pro architektonické osvětlení ColorGrazе MX Powercore BCS459 (RGB, 914 mm)</p>

Product details



ColorGrazе MX Powercore

Product details

OPDP_BCS459i_0021-Detail
photo



OPDP_BCS459i_0001-Detail
photo



OPDP_BCS459i_0003-Detail
photo



ColorGrazе MX Powercore 4ft ALT
2 Detail Shot

