



ColorBlast RGB Powercore gen4 – maximum control of color

ColorBlast RGB Powercore gen4

ColorBlast RGB Powercore gen4 is the next generation of indoor and outdoor floodlighting. Ideally suited for wall washing, grazing and spot lighting, ColorBlast RGB Powercore gen4 is a high-performance fixture that provides the benefits of fully saturated colors plus quality white light. It also offers a range of field-configurable beam angles, as well as the flexibility of customization with a full range of accessories that can be used in endless configurations.

Benefits

- Higher lumen output for a dynamic color fixture
- Color flexibility and consistency
- Complete set of accessories

Features

- Powercore technology directly accepts line voltage
- Light output of 1,750 lumens, full RGB
- Optional spread lenses of 20°, 40°, 60°, 80°, and 10° x 40° asymmetric
- Rugged mounting bracket allows simple positioning and fixture rotation
- Clean design of flat front to eliminate water pooling

Application

- Buildings facades
- Monuments and sculptures
- Parks and gardens
- Bridges and structures

ColorBlast RGB Powercore gen4

Versions



Product details

Blast Powercore gen4/gen5, RGBA
four channel LED fixture back view



Blast Powercore gen4/gen5, RGBA
four channel LED fixture front view



Blast Powercore gen4/gen5, RGBA
four channel LED fixture side view

