



# ColorBlast IntelliHue Powercore gen4 - high-quality tunable white light

## ColorBlast IntelliHue Powercore gen4

ColorBlast IntelliHue Powercore gen4 combines precision color control with high-quality tunable white light in one outdoor luminaire for wall-washing and spotlighting applications. IntelliHue, an advanced approach to color control and mixing, produces an enhanced spectrum of precisely controllable light, including millions of saturated colors, pastels, and precisely controllable, high-quality white and tinted white light. By combining carefully selected channels of LED light sources, IntelliHue enables high-quality intelligent color and white light from the same fixture. The fixture's completely flat front lens creates a minimalist, clean design and prevents any water pooling or debris accumulation, so the light is never interrupted. There is a full set of accessories that can be used in combination or alone, including a full-height glare shield, half-glare shield, louver, rock guard, and diffusers to alter the beam from 10° up to 80°.

### Benefits

- Higher color rendering for façade lighting
- Color flexibility and consistency
- Complete set of accessories

# ColorBlast IntelliHue Powercore gen4

## Features

- Powercore technology directly accepts line voltage
- Optional spread lenses of 20°, 40°, 60°, 80°, and 10° x 40° asymmetric
- High-quality tunable white and colored light in the same fixture, enabling tinting of any color temperature between 2000 and 10,000 K above and below the black-body curve
- Light output of 200–1500 lumens at CRI of >80 in the 2700–4000 K range
- Superior color consistency and accuracy with OptiBin and Chromasync technologies

## Application

- Building facades
- Monuments and sculptures
- Parks and gardens
- Bridges and structures

## Versions

Přisazené LED svítidlo ColorBlast  
IntelliHue gen4 Powercore  
BCP483



# ColorBlast IntelliHue Powercore gen4

## Product details

Colors available for housing



Front view



Rear view



Side view



Blast IntelliHue Powercore gen4  
surface-mounted LED fixture front  
view

