



Product Description

Plusline Small

Mains-voltage linear lamp giving white halogen light

Benefits

- Bright halogen light
- Bright halogen light
- Long lifetime
- Long lifetime

Features

- Clear tubular quartz bulb
- Clear tubular quartz bulb
- Reinforced filament supports for maximum safety and shock resistance resulting in longer lifetime
- Reinforced filament supports for maximum safety and shock resistance resulting in longer lifetime
- Two arc-preventing fuses for greater safety
- Two arc-preventing fuses for greater safety
- Excellent colour rendering
- Excellent colour rendering
- Constant light output during life
- Constant light output during life

Application

- Typically used in shop lighting applications
- Typically used in shop lighting applications
- Indoor: homes, offices, shops and museums
- Indoor: homes, offices, shops and museums
- Outdoor: billboards, car parks, security lighting and construction sites
- Outdoor: billboards, car parks, security lighting and construction sites