



Trusted quality for best performance

Essential MV MR16 Alu

The Essential MV MR16 Alu is part of the Philips "Value for Money" ranges. It is ideal for professional end-users looking for accent light - without a transformer - to create contrast in shops, hotels and restaurants.

优点

- Accent light to create the perfect focus on the objects to be lit
- Aluminum reflector to direct most of the heat to the front, ideal for heat-sensitive ceilings and luminaires
- Best dimmability to meet different brightness requirements

特点

- Bright sparkling light to create ambient atmosphere.
- Excellent color rendering (Ra=100) to present the true color of objects.
- Instant start to offer direct brightness from the moment switch on.
- No mercury to ensure the safety usage.
- Reliable quality to be trusted.

应用


- Shops, hotels and restaurants

Essential MV MR16 Alu

Versions



二维绘图



Product	D (max)	C (max)
ESS MR16 Alu 50W GU10 240V 36D 1CT	51 mm	51 mm

