



Product Description

CLASSICTONE Candle

Flame-shaped bulb with clear or inside-frosted glass and vacuum- or gas-filled bulb

Benefits

- Clear lamps: at their best in decorative glass chandeliers and wall lamps with clear or textured glass bowls. Brilliant, visible filament adds small points of brightness for an enriched lighting effect
- Frosted lamps: graceful lamps that enhance the elegance of classical chandeliers, candelabras, wall lamps etc. Set the scene for cosiness and comfort, used with or without lampshades

Features

- Clear lamps: slender, crystal-clear lamps designed for sparkling highlights that create a classic sparkling atmosphere
- Frosted lamps: slender, frosted lamps that create a low-glare atmosphere
- Universal burning position except for some 60W types which must be operated vertically, base-down (tolerance 90°)

Application


- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Ballrooms
- Shops and boutiques
- Churches

CLASSICTONE Candle

Versions



Dimensional drawing



Product	D	C (max)
CLAS 25W E14 240V B35 CL 1CT/10X10F	35 mm	100 mm

