



# Product Description

## PARTYTONE PAR38 Colour

Coloured pressed-glass 121 mm diameter reflector lamp

### Benefits

- Gives striking decorative effects, both indoors and outdoors
- 20% lower power consumption compared with conventional coloured PAR lamps

### Features

- Weatherproof silicon lacquer coating on the refractor face in a choice of colours
- Flood beam width

### Application


- Parks, public and private gardens
- Festive illumination
- Restaurants, bars, dance halls, nightclubs
- Show-window displays, fountains and 'Son et Lumiere' spectacles
- Can be installed outdoors without any protection, provided they are used in a watertight lampholder
- For outdoor use, a heat-resistant rubber ring must be fitted between the lamp and the lampholder

PARTYTONE PAR38 Colour

Versions



Dimensional drawing



Product	D	C (max)
PARTYTONE 80W E27 240V PAR38 Red 1CT/6	122.5 mm	137 mm
PARTYTONE 80W E27 240V PAR38 Green 1CT/6	122.5 mm	137 mm

Controls and Dimming	
Dimmable	yes
Operating and Electrical	
Voltage (Nom)	240 V
Power (Rated) (Nom)	80 W
Starting Time (Nom)	0.0 s
General Information	
Cap-Base	E27
Nominal Lifetime (Nom)	2000 h
Operating Position	UNIVERSAL
Rated Lifetime (Hours)	2000 h
Mechanical and Housing	
Bulb Shape	PAR38

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish
923811145582	PARTYTONE 80W E27 240V PAR38 Green 1CT/6	Green
923811245582	PARTYTONE 80W E27 240V PAR38 Red 1CT/6	Red

## PARTYTONE PAR38 Colour

