



Product Description

PARTYTONE PAR38 Colour

Coloured pressed-glass 121 mm diameter reflector lamp

Benefits

- Gives striking decorative effects, both indoors and outdoors
- 20% lower power consumption compared with conventional coloured PAR lamps

Features

- Weatherproof silicon lacquer coating on the refractor face in a choice of colours
- Flood beam width

Application


- Parks, public and private gardens
- Festive illumination
- Restaurants, bars, dance halls, nightclubs
- Show-window displays, fountains and 'Son et Lumiere' spectacles
- Can be installed outdoors without any protection, provided they are used in a watertight lampholder
- For outdoor use, a heat-resistant rubber ring must be fitted between the lamp and the lampholder

PARTYTONE PAR38 Colour

Versions



Dimensional drawing



Product	D (max)	C (max)
PARTYTONE 80W E27 230V PAR38 Yellow 1CT/12	123 mm	137 mm

