



Product Description

SPOTONE Ring Mirror Standard

Normal incandescent lamps with an internal ring-shaped parabolic aluminium mirror behind the filament

Benefits

- Beam spread and luminous intensity make these lamps especially suitable wherever space is limited and in small luminaires

Features

- Blown glass bulb with clear or frosted front
- Satin frosted version produces a soft, diffuse light
- Lamp is designed to achieve brilliant indoor lighting effects

Application

- Homes, shops, shop windows and displays, restaurants, hotels, exhibitions, bars and night clubs


Versions



E27, E80

SPOTONE Ring Mirror Standard

Dimensional drawing



Product	D	C (max)
SPOTONE 60W E27 240V E80 80D FR 1CT/6	80 mm	114.5 mm

