



# Product Description

## SPOTONE Ring Mirror Spotlight

Reflector lamps based on advanced spotlighting technology

### 优点

- Centre-beam intensities up to 100% higher than with conventional reflector lamps

### 特点

- Optic gives double reflection of part of the light emitted by the filament
- Beam spread and luminous intensity make these lamps especially suitable wherever space is limited and in small luminaires
- Wide choice of diameters and wattages
- Direct replacement for conventional reflector lamps of all kinds
- Easy fitting and removal thanks to tapered profile
- Universal burning position

### 应用


- All the benefits of high-performance, high-efficiency spotlighting, simply by replacing conventional reflector lamps with ring mirror lamps of the same size and wattage
- Display lighting in shops, hotels, restaurants and homes

# SPOTONE Ring Mirror Spotline

## Versions



## 二维绘图



| Product                                  | D     |
|--|-------|
| SPOTONE 40W E27 220-240V NR63 30D FR 1CT | 63 mm |

