



OneSpace luminous ceiling prefab - re-think the ceiling

OneSpace luminous ceiling prefab

Many business customers want a lighting solution that recalls the feeling of natural daylight, creating a calm and peaceful environment. They want great functional lighting that feels as good as it looks. Philips OneSpace luminous ceiling prefab is an impressive ultra-thin and compact standard unit with an excellent uniform light distribution. It also helps improve the acoustics in a room and meets the most stringent fire safety standards. The result is a ceiling unit that produces an amazing light effect while the light source remains hidden from view. With its minimalistic design, this slim, compact unit will blend in perfectly with any interior.

Benefits

- Glare-free light distribution that prevents shadows
- Enhanced room acoustics thanks to noise reduction
- Integrates perfectly with building management systems (DALI/Dynalite)

Features

- Easy-to-install ultra-thin panel
- Superior homogeneous light with fully concealed light source
- Textile front fabric, industry-leading fire class safety rating B
- Dimmable (DALI-controlled)
- Minimalistic design

Application

- General functional lighting for:
- Retail stores (flagships) and shopping malls
- Offices and meeting rooms
- Reception areas
- Large spaces like museums and airports

OneSpace luminous ceiling prefab

Specifications

Type	LP710P
Light source	Non-replaceable LED module
Power	190 W
Luminous flux	14000 lm
Correlated Color	3000 or 4000 K
Temperature	
Color Rendering Index	>80
Median useful life L70B50	50,000 hours
Average ambient temperature	+25 °C
Operating temperature range	+5 to +35 °C
Driver	Built-in
	Driver is placed in separate e-box on back of panel
Power/Data supply	2 x Xitanium 75 W and 1 x Xitanium 50 W
Mains voltage	220-240 V / 50-60 Hz

Dimming	DALI dimmable (10-100%)
Controls system input	Integrated
Material	Textile front: polyester
	Frame: aluminum
	Driver box: steel
	Acoustic absorber: mineral wool
Color	Textile front: off white
	Sides: graphite black (RAL 9011)
Connection	3 pole cable connector for mains, 2 pole for DALI
Maintenance	No cleaning or maintenance required
	Textile front NOT to be touched
Installation	4 brackets and bolts included to mount the panel to the ceiling, 4 hoisting brackets included to hoist panel to ceiling. Use white gloves.
	Additional special mounting sets available as accessory
	Through-wiring not possible

Versions



Product details

E-box mounted on rear of panel



OneSpace luminous ceiling prefab

Accessories

Mounting kit wire

Ordercode 07039000



Ordercode 07040600

